


DIN 1530  
1.2344 equivalent  
+  
Nitrided

# EJECTOR BLADES

— DIMENSIONS SPECIFY TYPE —



## D-ERNX



This product is not polished after nitriding.  
There is hardly any color unevenness, and no problem with the quality.

1.2344 equivalent + Nitrided  
Surface 900HV~ Material 40~45HRC

H	T	Part No. Type	D	0.01mm increments L	0.01mm increments P	0.01mm increments W	K max.	1mm increments N
4	2	D-ERNX	2	100.00 ~ 315.00	0.80 ~ 1.80	0.30 ~	1.9	N ≥ 30 and (L - N) ≥ 30
5	2.5		0.80 ~ 2.30	2.4				
6	3		0.80 ~ 2.80	2.9				
7	3.5		100.00 ~ 400.00	1.00 ~ 3.30	3.4			
8	3		4	100.00 ~ 500.00	1.00 ~ 3.80	3.9		
10	3		4.5	100.00 ~ 250.00	1.20 ~ 4.30	4.4		
			5	100.00 ~ 400.00	1.50 ~ 4.80	4.9		
12	5		5.5	100.00 ~ 200.00	1.80 ~ 5.30	5.4		
			6	100.00 ~ 1000.00	2.00 ~ 5.80	5.9		
			6.5	100.00 ~ 250.00	2.00 ~ 6.30	6.4		
14	5	8	2.50 ~ 7.80	7.9				
16		10	5.00 ~ 9.80	9.9				
18		12	100.00 ~ 1000.00	6.00 ~ 11.80	11.9			
22		16	8.00 ~ 15.80	15.9				
26	8	20	10.00 ~ 19.70	19.9				
32	10	25	100.00 ~ 500.00	13.00 ~ 24.70	24.9	N ≥ L/3, (L - N) ≥ 10		


Order **Part No.** - **L** - **P** - **W** - **N**  
D-ERNX12 - 505.00 - P10.00 - W5.00 - N170

Alterations **Part No.** - **L** - **P** - **W** - **N** - (AKC · AWC · etc.)  
D-ERNX12 - 505.00 - P10.00 - W5.00 - N170 - AKC 0

Alteration details P.3

Alterations	Code	Spec.	Alterations	Code	Spec.
	AKC	AKC = 1° increments 0 ≤ AKC < 360		ADC	ADC = 1° increments 0 ≤ ADC < 360
	AWC	AWC = 1° increments 0 ≤ AWC < 360		HC	HC = 0.1mm increments D + 1 ≤ HC < H
	ARC	ARC = 1° increments 0 ≤ ARC < 360		WR	2 places on top are rounded. Round process range is 20mm from the tip.
				FR	4 places on top are rounded. Round process range is 20mm from the tip.

### Precision Standard




DIN 1530  
1.2344 equivalent  
Hardened

# EJECTOR BLADES

— DIMENSIONS SPECIFY TYPE —



## D-ERDX



1.2344 equivalent  
50~55HRC

H	T	Part No. Type	D	0.01mm increments L	0.01mm increments P	0.01mm increments W	K max.	1mm increments N
4	2	D-ERDX	2	100.00 ~ 315.00	0.80 ~ 1.80	0.30 ~	1.9	N ≥ 30 and (L - N) ≥ 30
5	2.5		0.80 ~ 2.30	2.4				
6	3		0.80 ~ 2.80	2.9				
7	3.5		100.00 ~ 400.00	1.00 ~ 3.30	3.4			
8	3		4	100.00 ~ 500.00	1.00 ~ 3.80	3.9		
10	3		4.5	100.00 ~ 250.00	1.20 ~ 4.30	4.4		
			5	100.00 ~ 400.00	1.50 ~ 4.80	4.9		
12	5		5.5	100.00 ~ 200.00	1.80 ~ 5.30	5.4		
			6	100.00 ~ 1000.00	2.00 ~ 5.80	5.9		
			6.5	100.00 ~ 250.00	2.00 ~ 6.30	6.4		
14	5	8	2.50 ~ 7.80	7.9				
16		10	5.00 ~ 9.80	9.9				
18		12	100.00 ~ 1000.00	6.00 ~ 11.80	11.9			
22		16	8.00 ~ 15.80	15.9				
26	8	20	10.00 ~ 19.70	19.9				
32	10	25	100.00 ~ 500.00	13.00 ~ 24.70	24.9	N ≥ L/3, (L - N) ≥ 10		

Order **Part No.** - **L** - **P** - **W** - **N**  
D-ERDX5 - 120.25 - P3.50 - W1.50 - N60

Alterations **Part No.** - **L** - **P** - **W** - **N** - (AKC · AWC · etc.)  
D-ERDX5 - 120.25 - P3.50 - W1.50 - N60 - AWC60

Alteration details P.3

Alterations	Code	Spec.	Alterations	Code	Spec.
	AKC	AKC = 1° increments 0 ≤ AKC < 360		ADC	ADC = 1° increments 0 ≤ ADC < 360
	AWC	AWC = 1° increments 0 ≤ AWC < 360		HC	HC = 0.1mm increments D + 1 ≤ HC < H
	ARC	ARC = 1° increments 0 ≤ ARC < 360		WR	2 places on top are rounded. Round process range is 20mm from the tip.
				FR	4 places on top are rounded. Round process range is 20mm from the tip.

### Precision Standard

