

Slit Steel Pipe Nozzles / Nozzles for Pipe Washing

Steel Hollows for Air Nozzles / Terminals for Nozzles

Slit Steel Pipe Nozzles

Type	Material	Surface Treatment	Accessory:
Threaded and Tapped Both Ends Tapped	EN 1.0305 Equiv.	Zinc Plating	Tapered Screw Plug (EN 1.7220 Equiv., Black Oxide) 1 pc.
SLTR	EN 1.4301 Equiv.	-	Tapered Screw Plug (EN 1.4567 Equiv.) 1 pc.
SLTF	-	-	-
SLTRS	-	-	-
SLTFS	-	-	-


Accessory Tapered Screw Plug is seal-coated.

RoHS10

Part Number Type	L 1mm Increment	A 1mm Increment	T 0.5mm Increment	R (PT)	T ₁	T ₂	D	d	SLTR, SLTF Unit Price			SLTRS, SLTFS Unit Price		
									Min. L ~ 250	L251~500	L501~700	Min. L ~ 250	L251~500	L501~700
Threaded and Tapped SLTR SLTRS	6A	90~700	50~500	0.5~2.0	1/8	10	11	10.5	-	-	-	-	-	-
	8A	100~700			1/4	15	13	13.8	9.2	7.8	-	-	-	-
	10A				3/8	17	16	17.3	12.7	10.9	-	-	-	-
Both Ends Tapped SLTF SLTFS	15A	110~700	1/2	20	18	21.7	16.1	16.1	-	-	-	-		
	20A		3/4	23	20	27.2	21.6	21.4	-	-	-	-		
	25A		1	25	22	34	27.6	27.2	-	-	-	-		

Ordering Example: Part Number - L - A - T
SLTR8A - 300 - A200 - T1.0

There is no surface treatment on threaded part and slit machining and its peripheral part. * Marks may be left on the surface when tightening screws.
Excessive tightening may deform the female thread portion. Wrap with sealing tape for air tightness and after manual tightening, tighten it up further by giving one rotation or so.



Features: Simple nozzles with a slit in a pipe. Suitable when the distance to the object is short.

Precaution for Use: Actual spray width and colliding force vary. And the slit width may increase depending on air pressure. When more even blows are required, use Air Nozzles (P.1455) and Steel Hollows for Air Nozzles (P.1474).

The drawing of the app. example is a reference image.



Nozzles for Pipe Washing

PWNZR

RoHS10

Part Number Type	No.	H	Cover Dimension				Body Dimension				P.C.D.	Applicable Max. Pipe O.D. 1 ~ 20 pc(s)	Unit Price
			B ₁	B ₂	B ₃	B ₄	A ₁	A ₂	A ₃	A ₄			
PWNZR	10	49	26	28	40	57	34	36	42	57	49	Ø20	
	20	59	36	38	50	67	44	46	52	67	59	Ø30	

Ordering Example: Part Number PWNZR10



Step
1 Insert the pipe into the nozzle to clean it.
2 Apply the air pressure from both sides by an air compressor, and air will out-flow evenly from internal clearance (0.3mm).

Specifications
Nozzle Air Pressure MPa (kg/cm²) when service air pressure is 0.69MPa (7kg/cm²).
• No.10 0.15(1.54)
• No.20 0.11(1.19)

Use for blowing around cylindrical workpiece (pipe, etc.).

Features: Can be used as air curtains when combined with Flat Type Air Nozzle on P.1455.

Steel Hollows for Air Nozzles

Type	Material	Surface Treatment	Normal Pressure	Accessory:
Threaded and Tapped Both Ends Tapped	EN 1.0305 Equiv.	Zinc Plating	0.7MPa	Tapered Screw Plug (EN 1.7220 Equiv., Black Oxide) 1 pc.
AMR	EN 1.4301 Equiv.	-	-	Tapered Screw Plug (EN 1.4567 Equiv.) 1 pc.
AMRS	-	-	-	-
AMF	-	-	-	-
AMFS	-	-	-	-

Accessory Tapered Screw Plug is seal-coated.



RoHS10

Part Number Type	No.	Pitch P 1mm Increment	S, Q 1mm Increment	AMR, AMF Unit Price					AMRS, AMFS Unit Price					
				H1, 2	H3, 4	H5, 6	H7, 8	H9, 10	H1, 2	H3, 4	H5, 6	H7, 8	H9, 10	
Threaded and Tapped Both Ends Tapped	20A	1~10	60~80	35~80										
AMR	AMF													
AMRS	AMFS													

When H (the number of side tapped holes) is 1, specifying Pitch P is not necessary.

Part Number	H (Number of Holes)	P	S	Q
AMR20A	1	-	S40	Q50
AMF20A	8	P70	S35	Q35

Spray Width Property Table



Terminals for Nozzles Clamp Type

NZTA

RoHS10

Part Number Type	D	No.	Rc(PT)	B	L	E	G	H	F	MA	d	d ₁	h	W	Included Bolt	Unit Price
10	H	-	16	30	13.5	16.5	8.5	10	M4	4.5	8	4.5	1.5	SCB4-10		
12	H	1/8	18	40	15	25	10	16	M4	4.5	8	4.5	1.5	SCB4-10		
15	H	1/4	22	52	19	33	13	22	M5	5.5	9.5	5.5	1.5	SCB5-15		

Terminals for Nozzles Block Type

NZTB

RoHS10

Part Number Type	No.	Unit Price
NZTB	1	
	2	
	1-1	
	1-2	

