

DIN 1530
1.2344 equivalent
+
Nitrided


EJECTOR BLADES

— DIMENSIONS SPECIFY TYPE —


DIN 1530
1.2344 equivalent
Hardened

EJECTOR BLADES

— DIMENSIONS SPECIFY TYPE —



D-ERNX



⚠ This product is not polished after nitriding.
There is hardly any color unevenness, and no problem with the quality.

Ⓜ 1.2344 equivalent + Nitrided
Ⓜ Surface 900HV~ Material 40~45HRC

H	T	Part No. Type	D	0.01mm increments L	0.01mm increments P	0.01mm increments W	K max.	1mm increments N
4	2	D-ERNX	2	100.00 ~ 315.00	0.80 ~ 1.80	0.30 ~	1.9	N ≥ 30 and (L-N) ≥ 30
5			2.5	100.00 ~ 315.00	0.80 ~ 2.30		2.4	
6			3	100.00 ~ 400.00	0.80 ~ 2.80		2.9	
7	3.5		100.00 ~ 400.00	1.00 ~ 3.30	3.4			
8	3		4	100.00 ~ 500.00	1.00 ~ 3.80	0.40 ~	3.9	
10			4.5	100.00 ~ 250.00	1.20 ~ 4.30		4.4	
12			5	100.00 ~ 400.00	1.50 ~ 4.80		4.9	
14	5		5.5	100.00 ~ 200.00	1.80 ~ 5.30	0.50 ~	5.4	
16			6	100.00 ~ 1000.00	2.00 ~ 5.80		5.9	
18			6.5	100.00 ~ 250.00	2.00 ~ 6.30		6.4	
22		8	100.00 ~ 1000.00	2.50 ~ 7.80	1.00 ~		7.9	
26		10		5.00 ~ 9.80			9.9	
32	12	6.00 ~ 11.80		11.9				
	7	16	8.00 ~ 15.80	15.9	· D10~D16 N ≥ 50 · D20~D25 N ≥ 55 and N ≥ L/3, (L-N) ≥ 10			
	8	20	10.00 ~ 19.70	19.9				
	10	25	100.00 ~ 500.00	13.00 ~ 24.70	24.9			



Order Part No. — L — P — W — N
D-ERNX12 — 505.00 — P10.00 — W5.00 — N170

Alterations Part No. — L — P — W — N — (AKC · AWC · etc.)
D-ERNX12 — 505.00 — P10.00 — W5.00 — N170 — AKC 0


Alteration details P.4

Alterations	Code	Spec.	Alterations	Code	Spec.
	AKC	AKC=1° increments 0 ≤ AKC < 360		ADC	ADC=1° increments 0 ≤ ADC < 360
	AWC	AWC=1° increments 0 ≤ AWC < 360		HC	HC=0.1mm increments D+1 ≤ HC < H
	ARC	ARC=1° increments 0 ≤ ARC < 360		WR	2 places on top are rounded. Round process range is 20mm from the tip.
				FR	4 places on top are rounded. Round process range is 20mm from the tip.

■ Precision Standard



D-ERDX



Ⓜ 1.2344 equivalent
Ⓜ 50~55HRC

H	T	Part No. Type	D	0.01mm increments L	0.01mm increments P	0.01mm increments W	K max.	1mm increments N
4	2	D-ERDX	2	100.00 ~ 315.00	0.80 ~ 1.80	0.30 ~	1.9	N ≥ 30 and (L-N) ≥ 30
5			2.5	100.00 ~ 315.00	0.80 ~ 2.30		2.4	
6			3	100.00 ~ 400.00	0.80 ~ 2.80		2.9	
7	3.5		100.00 ~ 400.00	1.00 ~ 3.30	3.4			
8	3		4	100.00 ~ 500.00	1.00 ~ 3.80	0.40 ~	3.9	
10			4.5	100.00 ~ 250.00	1.20 ~ 4.30		4.4	
12			5	100.00 ~ 400.00	1.50 ~ 4.80		4.9	
14	5		5.5	100.00 ~ 200.00	1.80 ~ 5.30	0.50 ~	5.4	
16			6	100.00 ~ 1000.00	2.00 ~ 5.80		5.9	
18			6.5	100.00 ~ 250.00	2.00 ~ 6.30		6.4	
22		8	100.00 ~ 1000.00	2.50 ~ 7.80	1.00 ~		7.9	
26		10		5.00 ~ 9.80			9.9	
32	12	6.00 ~ 11.80		11.9				
	7	16	8.00 ~ 15.80	15.9	· D10~D16 N ≥ 50 · D20~D25 N ≥ 55 and N ≥ L/3, (L-N) ≥ 10			
	8	20	10.00 ~ 19.70	19.9				
	10	25	100.00 ~ 500.00	13.00 ~ 24.70	24.9			

Order Part No. — L — P — W — N
D-ERDX5 — 120.25 — P3.50 — W1.50 — N60

Alterations Part No. — L — P — W — N — (AKC · AWC · etc.)
D-ERDX5 — 120.25 — P3.50 — W1.50 — N60 — AWC60

Alteration details P.4

Alterations	Code	Spec.	Alterations	Code	Spec.
	AKC	AKC=1° increments 0 ≤ AKC < 360		ADC	ADC=1° increments 0 ≤ ADC < 360
	AWC	AWC=1° increments 0 ≤ AWC < 360		HC	HC=0.1mm increments D+1 ≤ HC < H
	ARC	ARC=1° increments 0 ≤ ARC < 360		WR	2 places on top are rounded. Round process range is 20mm from the tip.
				FR	4 places on top are rounded. Round process range is 20mm from the tip.

■ Precision Standard

