

Hinge Bases

Side Mounting U-Shaped


■ **Features:** U-Shaped and side mounting can reduce the height.




RoHS10

H Configurable		W and H Configurable		M	S	A
H7 Type	H7 Type with Tap	H7 Type	H7 Type with Tap	Material	Surface Treatment	Accessory
HKSUB	HKSUBT	HGSUB	HGSUBT	EN 1.1191 Equiv.	Black Oxide	Set Screws 2 pcs. (EN 1.4301 Equiv.)
HKSUM	-	-	HGSUMT	EN 1.4301 Equiv.	Electroless Nickel Plating	-
HKSUS	-	HGSUS	-	-	-	-

H Configurable



W and H Configurable



⚠ For H7 Type, M part doesn't have tap and set screw. ⚠ Holes for D=2 are through holes, not counterbored.

H Configurable		Unit Price										
Part Number	H	Unit Price										
Type	DH7	1mm Increment	W	A	F	B	K	T	d	d1	H1	M
(H7)	2	15~20	4	13	7	H+3	10	6	-	-	-	-
	3	20~25	6	16	8	H+5		9	3.5	6.5	3.5	M3
	4	25~30	8	19	11	H+6	12	12	4.5	8	4.5	M4
	5		10	25	16	H+8		16	5.5	9.5	5.5	M5
	6		12	32	20	H+10	14	19	5.5	9.5	5.5	M6
(H7 Type with Tap)	8	30~40	10	50	38	H+10	15	22	6.5	11	6.5	M4
	10		12		36	H+12		25	6.5	11	6.5	M5
	12		16	36	H+12	15	22	25	6.5	11	6.5	M6
	14	35~45	20	65	47	H+14	18	30	9	14	9	M6
	16		25		47	H+17		30	9	14	9	M6

⚠ For detailed dimensions of Hinge Pin, see P.1-908.

W and H Configurable		Unit Price										
Part Number	W	H	Unit Price									
Type	DH7	1mm Increment	5mm Increment	A	F	B	K	T	d	d1	H1	M
(H7)	2	3~5	15~20	13	7	H+3	10	6	-	-	-	-
	3	3~9	20~25	16	8	H+5		9	3.5	6.5	3.5	M3
	4	4~12	25~30	19	11	H+6	12	12	4.5	8	4.5	M4
	5	5~15		25	16	H+8		16	5.5	9.5	5.5	M5
	6	6~18		32	20	H+10	14	19	5.5	9.5	5.5	M6
(H7 Type with Tap)	8	8~24	30~40	38	26	H+10	15	22	6.5	11	6.5	M4
	10	10~30		50	36	H+12		25	6.5	11	6.5	M5
	12	12~30			36	H+12	15	22	6.5	11	6.5	M6
	13	13~30	35~45	65	47	H+14	18	30	9	14	9	M6
	14	14~30			47	H+17		30	9	14	9	M6

⚠ For detailed dimensions of Hinge Pin, see P.1-908.

⚠ For H7 type with tap, (A-W)/2≥M+2 is required.



Ordering Example

Part Number - H


HKSUB10 - H33

Part Number - W - H

HGSUB10 - W16 - H35



■ **Features:** Side mounting allows to reduce height.



Hinge Bases

Side Mounting T-Shaped


■ **Features:** T-Shaped Side Mounting Type.




RoHS10

H Configurable		M	S	A
H7 Type	H7 Type with Tap	Material	Surface Treatment	Accessory
HKSBB	HKSBBT	EN 1.1191 Equiv.	Black Oxide	Set Screws 1 pc. (EN 1.4301 Equiv.)
HKSBS	-	EN 1.4301 Equiv.	-	-

M (H7 Type with Tap only)



2-C2



⚠ For H7 Type, M part doesn't have tap and set screw. ⚠ Holes for D=2 are through holes, not counterbored.

H Configurable		Unit Price										
Part Number	H	Unit Price										
Type	DH7	1mm Increment	W	A	F	B	K	T	d	d1	H1	M
(H7)	2	15~20	4	13	7	H+3	10	6	-	-	-	-
	3	20~25	6	16	8	H+5		9	3.5	6.5	3.5	M3
	4	25~30	8	19	11	H+6	12	12	4.5	8	4.5	M4
	5		10	25	16	H+8		16	5.5	9.5	5.5	M5
	6		12	32	20	H+10	14	19	5.5	9.5	5.5	M6
(H7 Type with Tap)	8	30~40	10	50	38	H+10	15	22	6.5	11	6.5	M4
	10	35~45	12		36	H+12		25	6.5	11	6.5	M5
	12	40~50	16	65	47	H+14	18	30	9	14	9	M6
	14		20		47	H+17		30	9	14	9	M6
	16		25									

⚠ For detailed dimensions of Hinge Pin, see P.1-908.



Ordering Example

Part Number - H

HKSBB6 - H30

