

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 24_BNC-75-4-3/133_N

Rev.: C



Description

Straight bulkhead cable feed through

Interface Standards

IEC 60169-8_MIL-STD-348A/301_CECC 22120

Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0167 kg

Environmental Data

Operating Temperature	-65 °C to 165 °C
2002/95/EC (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	MVQ (Silicone Rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00071754
Catalogue drawing	DCA-00008930
Assembly instruction	DOC-0000179061
Mounting hole	DOU-00008751

Ordering Information

Single package 24_BNC-75-4-3/133_NE

Additional Information

Suitable cables RG_59_B/U, GX_04273

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions