

Stopper Blocks

CAD Data

RoHS

■ Straight Type

Type	Counterbore Hole	Drill Hole	□	□	□
SBHB	SBKHB		1.1191/	-	Black Oxide
SBHM	SBKHM		-	-	Electroless Nickel Plating
SBHNB	SBKHNB	C45E	40HRC~	-	Black Oxide
SBHNM	SBKHNM		40HRC~	-	Electroless Nickel Plating
SBHU		Urethane	Shore A90	-	-
SBHJ			Polyacetal	-	-

Part Number	A Selection	H 5mm Increment	T Counterbore Hole	T Drill Hole	X	d1	d2	ℓ1	T	Unit Price				Qty. 1~4		
										SBHB	SBHM	SBHNB	SBHNM	SBHU	SBHJ	
(Counterbore Hole)	(Drill Hole)	20 30 40 50	(5)10~40	10	10	5	8	4.5	4.5	10 · A10	7,30	8,70	10,70	12,60	7,70	10,70
SBHB	SBKHB	30 40 50 60	(10)15~50	15	A10	7	9.5	5.5	5.5	15 · A15	11,00	13,40	16,00	19,40	11,20	12,80
SBHM	SBKHM	30 40 50 60 70 80	(15)20~50	20	15	8	11	6.5	6.5	20	14,10	16,90	20,50	24,50	13,70	15,90
SBHNB	SBKHNB	40 50 60 70 80 90 100	(20)30~50	30	A15	10	14	9	9	30	14,80	17,70	21,50	25,70	14,40	17,90

RoHS

■ Tapped Hole Type

Type	With Counterbores, Tapped Hole	With Tapped Hole	□	□	□
SBNB	SBKNB		1.1191/	-	Black Oxide
SBNM	SBKNM		-	-	Electroless Nickel Plating
SBNNB	SBKNNB	C45E	40HRC~	-	Black Oxide
SBNNM	SBKNNM		40HRC~	-	Electroless Nickel Plating

Part Number	A Selection	H 5mm Increment	T Counterbore and Tap	T With Tap	X	d1	d2	ℓ1	N	T	Unit Price				Qty. 1~4	
											SBNB	SBNM	SBNNB	SBNNM	SBKNB	SBKNM
(With Counterbores, Tapped Hole)	(With Tapped Hole)	20 30 40 50	(5)10~40	10	10	5	8	4.5	4.5	M5	10 · A10	9,30	10,70	12,70	14,60	
SBNB	SBKNB	30 40 50 60	(10)15~50	15	A10	7	9.5	5.5	5.5	M6	15 · A15	13,00	15,40	18,00	21,40	
SBNM	SBKNM	30 40 50 60 70 80	(15)20~50	20	15	8	11	6.5	6.5	M8	20	16,10	18,90	22,50	26,50	
SBNNB	SBKNNB	40 50 60 70 80 90 100	(20)30~50	30	A15	10	14	9	9	M10	30	16,80	19,70	23,50	27,70	

RoHS

■ Plate type

Type	□	□	□
SBFB	1.1191/	-	Black Oxide
SBFM	C45E	-	Electroless Nickel Plating
SBFNB		40HRC~	Black Oxide
SBFNM		40HRC~	Electroless Nickel Plating

Part Number	A Selection	H 5mm Increment	T	X	d1	d2	ℓ	Unit Price				Qty. 1~4	
								SBFB	SBFM	SBFNB	SBFNM		
SBFB	20 30 40 50	10~30	5	5	-	5.5	-	5,10	6,10	7,50	9,00		
SBFM	20 30 40 50 60	10~40	8	5	8	4.5	4.5	7,80	9,50	11,30	13,80		
SBFNB	30 40 50 60 70 80	15~50	10	7	9.5	5.5	5.5	9,90	12,00	14,30	17,30		
SBFNM	30 40 50 60 70 80 90 100	20~50	15	8	11	6.5	6.5	10,30	12,40	15,00	18,10		

Order Example: Part Number SBKHB - 40 - 10 - A10

Days to Ship: 8 Days

Price: Volume Discount P.92

Stopper Blocks with Urethane/Adjusting Pins

CAD Data

RoHS

■ Stopper Blocks with Urethane

Type	Urethanes	□	□	□
SBUB	Shore A90 (Natural Color)	1.1191/	-	Black Oxide
SBUM		C45E	-	Electroless Nickel Plating

Urethane is baked.
Surface treatment of verge part between core block and urethane may be peeled off about 2~3mm from edge.

Part Number	Type	A Selection			H Selection			T	X	d1	d2	ℓ	Unit Price		Qty. 1~9	
		SBUB	SBUM		SBUB	SBUM							SBUB	SBUM		
SBUB		30	40	50	20	25	30	40	50	15	7	9.5	5.5	5.5	23,60	25,40
SBUM		30	40	50						20	8	11	6.5	6.5	27,40	29,70
		40	50	60						30	10	14	9	9	29,30	31,60

Order Example: Part Number SBUB - 40 - 20 - 15

Days to Ship: 10 Days

Price: Volume Discount P.92

RoHS

■ Stopper Blocks with Urethane Cylinder Type

Type	Urethanes	□	□	□
SBEB	Shore A90 (Black)	1.1191/	-	Black Oxide
SBEM		C45E	-	Electroless Nickel Plating

Urethane is baked.
Surface treatment of verge part between core block and urethane may be peeled off about 2~3mm from edge.

Part Number	Type	D	H Selection				M (Coarse)	W	ℓ	Unit Price		Qty. 1~9	
			SBEB	SBEM						SBEB	SBEM		
SBEB		10	20	25	30	35	40	6	8	8	9,70	10,10	
SBEM		20	25	30	35	40	10	17	10	11,90	12,90		
		30	30	35	40	12	27	15	16,20	18,50			

RoHS

■ Adjusting Pins

AJP (Retaining Ring Type)

AJPB (Lock Nut Type)

D	A	B	E	C	S
3	5.5	2.5	3.5	0.5	1
4	7	3	4.5	0.7	1.4
5	8.5	4	5.5	1	2
6	10	5	6.5	1.3	2.6
8	13	6	8.5	1.6	3.2

S dimension is maximum length of adjusting pins at 360° rotation by hexagon wrench.

Type	□	□
AJP	1.4301/	Retaining Ring
AJPB	X5CrNi18-10	1.4301/X5CrNi18-10

Part Number	Type	Dg6	L 1mm Increment	M1	Tolerance	N	d	Tolerance	Unit Price		Qty. 1~9	
									AJP	AJPB	AJP	AJPB
AJP		3	5(10)~20	0.5	+0.05/0	2	2	+0.06	5,50	8,30		
AJPB		4	5(10)~25			3	3		7,00	10,40		
		5	10~30	0.7	+0.1/0	2	4	+0.075/0	8,00	10,70		
		6	10~35			5	5		9,50	12,10		
		8	10~40	0.9	+0.14/0	3	7	+0.09/0	11,00	13,50		

Order Example: Part Number AJP3 - 6

Days to Ship: 8 Days

Price: Volume Discount P.92