

Between Series Adaptor 33_N-716-50-1/---_U

Description

Adaptor plug/jack
N plug (male) / 7/16 jack (female)

Interface standards
Series N - IEC 61169-16_MIL-STD-348A/304_CECC 22210
Series 7/16 - IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz
VSWR	DC - 7.5 GHz ≤ 1.03 + 0.02 f (GHz)

Mechanical Data

Number of matings	500
Weight	0.1015 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS)	compliant

Material Data

Interface - N plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - 7/16 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00014333
-------------------	--------------

Ordering Information

Single package	33_N-716-50-1/---_UE
----------------	----------------------