




Thick Hinge Bases Notched Type

-Standard · A Dimension Compact-

CAD Data

■ **Features:** Hinge base is added with A dimension (lateral) more compact than conventional hinges



Part Number	Type	DH7	W		H 1mm Increment	Standard			A Dimension Compact			K	S	d	C	€ Unit Price																															
			Standard	A Dimension Compact		Standard	A Dimension Compact	A	F	E	A					F	E	W Dimension Fixed	W, H Configurable																												
			Selectable	1mm Increment		Selectable	1mm Increment											HKNJB	HKNJM	HGNJB	HGNJM	HGNAJS																									
4-12	Standard	12	4-12	5	4-8	17-25	38	29	20	32	25	16	10																																		

* Dimensions in () are for A Dimension Compact Type. Price of A Dimension Compact (1.1191/C45E) is above price x 0.95 (rounded down to the nearest ten Cent).

Order Example: Part Number - T - W - H
 HKNJB6 - T19 - W25 - H27
 HG NJM20 - T38 - W25 - H48
 HGNAJB10 - T22 - W15 - H30
 Days to Ship: **8 Days**

Volume Discount (Round down to one Cent) P87

Quantity	Discount Rate	€ Unit Price
1-9	-	-
10-14	5%	-
15-19	10%	-

 For orders larger than indicated quantity, please request a quotation.

Comparison of A Dimensions

DH7	T	Prong T-Shape Type			Notched T-Shape Type		
		Standard Type (#P.1466)	A Dimension Compact	Reduction Ratio	Standard Type	A Dimension Compact	Reduction Ratio
4	12	25	22	-12%	38	32	-16%
5	16	32	25	-22%	50	38	-24%
6	16	32	25	-22%	50	38	-24%
8	19	38	32	-16%	65	50	-23%
10	19	38	32	-16%	65	50	-23%
12	22	50	38	-24%	75	65	-13%
13	22	50	38	-24%	75	65	-13%
14	25	50	38	-24%	75	65	-13%
15	25	50	38	-24%	75	65	-13%
16	30	65	50	-23%	100	75	-25%
20	30	65	50	-23%	100	75	-25%
25	38	65	50	-23%	100	75	-25%


Alterations: Part Number - T - W - H - (WDC)
 HKNJB6 - T19 - W25 - H27 - WDC

Alteration	Code	Spec.	Price Adder
	WDC	Changes the number of d holes from 2 to 4. The holes are drilled at T1 position. Ordering Code: WDC	3,00

Ordering Code: WDC
 T T1
 16 8
 19 10
 22 12
 25 14
 30 15
 38 20
 Not applicable to D4.

Thick Hinge Bases L-Shaped Type

CAD Data



Part Number	Type	DH7	T Selection	W 1mm Increment	H 1mm Increment	A	F	P	X	S	d2	d1	H1	C	€ Unit Price																									
															Prong Type		Notched Type																							
															HGLKB	HGLKM	HGLJB	HGLJM	HGLJS																					
4	Prong Type HGLKB HGLKM	4	12	4-8	20-30	25	12	12	18.5	7.5	4.5	8	4.5	3																										

Order Example: Part Number - T - W - H
 HGLKB10 - T19 - W15 - H35
 HGLKM16 - T30 - W25 - H42
 Days to Ship: **10 Days**
 Express B 5,00 EUR/ piece P88
 -1.1191/C45E
 -1.4301/X5CrNi18-10
 Express Charge of 13,50 EUR for 3 or more identical pieces.

Volume Discount (Round down to one Cent) P87

Quantity	Discount Rate	€ Unit Price
1-9	-	-
10-14	5%	-
15-19	10%	-

 For orders larger than indicated quantity, please request a quotation.

List of Diameter (DH7), Thickness (T) and Thickness on one side

DH7	Hinge Base Standard Type (P.1470-P.1479)			Hinge Base Thick Type		
	T	Thickness on one side (T-DH7)/2	T	Thickness on one side (T-DH7)/2	T	Thickness on one side (T-DH7)/2
4	9	2.5	12	4	-	-
5	12	3.5	16	5.5	19	7
6	12	3	16	5	19	6.5
8	16	4	19	5.5	22	7
10	16	3	19	4.5	22	6
12	19	3.5	22	5	25	6.5
13	19	3	22	4.5	25	6
14	19	4	22	5.5	25	8
15	22	3.5	25	5	30	7.5
16	22	3	25	4.5	30	7
20	25	2.5	30	5	38	9
25	30	2.5	38	6.5	-	-

■ Features: The hole's thickness on one side is selectable based on applied working load.