


Extension cable, Automation Line, M12x1



**Product data**

|                    |                |
|--------------------|----------------|
| Item description   | AL-WAK8-2/S370 |
| Item-No.           | 8046903        |
| Length             | 2m             |
| Customs tariff-No. | 85444290       |
| Step-File          | AL-WAK8.stp    |

**Technical data**

|                                |  |
|--------------------------------|--|
| Connector                      | female, M12x1, straight                        |
| Number of pins                 | 8  |
| Pin assignment                 | 1 WH, 2 BN, 3 GN, 4 YE, 5 GY, 6 PK, 7 BU, 8 RD |
| Coding                         | A  |
| Rated voltage                  | 30V  |
| Current load (at 40°C)         | 2A   |
| Insulation resistance          | $\geq 10^8 \Omega$                             |
| Resistance                     | $\leq 5 \text{ m}\Omega$                       |
| Ambient temperature product    | -30°C...+90°C                                  |
| Contact material               | Metal, CuZn, gold-plated                       |
| Contact-carrier material       | Plastic, TPU, BK                               |
| Grip body material             | Plastic, TPU, BK                               |
| Coupling nut material          | Metal, CuZn, nickel-plated                     |
| Sealing (female) material      | FPM/FKM  |
| Standards                      | IEC 61076-2-101                                |
| Degree of protection (mounted) | IP65, IP67, IP68                               |
| Mechanical life-cycle          | >100 mating cycles                             |
| Cable end assembly             | open cable end                                 |
| Degree of pollution            | 3  |

**Cable****S370**

Flexible, silicone- and halogen-free control line with high mechanical strength. The cable is chemicals, hydrolysis-, and microbes- resistant. The drag-chain application is possible at a bending radius of minimum 10 x d. Due to its weld-field immunity, the cable is very well suited for the flexible application in robotics, machine-tool, and metal-cutting production. The cables meet the UL and CSA (UL10493/20549; cULus) requirements.

|                                |  |
|--------------------------------|--|
| Outer diameter of jacket       | 5,90 mm  |
| Cable-jacket material          | PUR  |
| Jacket color                   | black, similar RAL9005   |
| Wire cross-section             | 8 x 0.25 mm <sup>2</sup>   |
| Wire insulation material       | PP   |
| Wire colors                    | WH, BN, GN, YE, GY, PK, BU, RD   |
| Conductor structure            | 32 x 0.10 mm   |
| Bending radius (fixed)         | 5 x Ø-cable  |
| Bending radius (repeated)      | 10 x Ø-cable   |
| Temperature range (repeated)   | -30°C...+90°C  |
| Temperature range (fixed)      | -40°C...+90°C  |
| Temperature range (drag chain) | -25°C...+60°C  |
| Halogen-free                   | Yes  |
| Rated voltage cable            | ≤300 V   |
| Special features               | flame retardant, seawater resistant, recyclable, LABS free, RoHs compliant, acid- and alkali resistant, ozone resistant, UV resistant, hydrolysis proof, drag chain-adapted, torsion resistant, welding sparks resistant, halogen free, silicone free, oil resistant |