

## Between Series Adaptor 33\_716-N-50-1/---\_U

### Description

Adaptor plug/jack  
7/16 plug (male) / N jack (female)

Interface standards  
Series 7/16 - IEC 61169-4\_CECC 22190\_DIN 47223\_VG 95250  
Series N - IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz
VSWR	DC - 7.5 GHz ≤ 1.03 + 0.02 f (GHz)

#### Mechanical Data

Number of matings	500
Weight	0.0928 kg

#### Environmental Data

Operating temperature 2011/65/EU (RoHS)	-65 °C to 165 °C compliant
--	-------------------------------

#### Material Data

Interface - 7/16 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Silver Plating
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - N jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Nickel Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing DOU-00014432

### Ordering Information

Single package 33\_716-N-50-1/---\_UE