



## Cable Ties outside serrated for marking

### • LR55-Series

#### Features and Benefits

The extended pawl allows for quick and simple release of the ties. Manufactured in various colours these cable ties are ideal for applications where colour coding is required. Additionally, the LR55 Series are outside serrated, minimising the risk of damage to cable insulation.

#### Application

These releasable and reusable ties are ideal where temporary installation or the addition or removal of cables is required, for example: logistic identification (colour coding), packaging industries, cable harness manufacturing.



The LR55 cable ties are reusable and ideal for colour coding.


#### Material Data

Material	<b>Polyamide 6.6 (PA66)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



#### Material Data

Material	<b>Polyamide 6.6 Heat Stabilised (PA66HS)</b>
Operating Temperature	<b>-40 °C to +105 °C Continuous, (+145 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



LR55 Series

#### Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour
115-00003	LR55R	195	4.7	50.0	245	PA66	Red (RD)
115-00004	LR55R	195	4.7	50.0	245	PA66	Yellow (YE)
115-00005	LR55R	195	4.7	50.0	245	PA66	Green (GN)
115-00006	LR55R	195	4.7	50.0	245	PA66	Blue (BU)
115-00008	LR55R	195	4.7	50.0	245	PA66	Natural (NA)
115-00002	LR55R	195	4.7	50.0	245	PA66HS	Black (BK)

All dimensions in mm. Subject to technical changes.