

# Bus system connector - SACC-M12MSD-4Q SH - 1543223

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Bus system connector, Ethernet CAT5, Ethernet CAT5e, 4-position, shielded, Plug straight M12, D-coded, Insulation displacement connection, Knurl material: Nickel-plated brass, External cable diameter 4 mm ... 8 mm

## Product Features

- Safe use in the field, thanks to a high degree of protection
- Flexible: connectors for on-site assembly
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire
- Reliable signal transmission - 360° shielding in environments with electromagnetic interference

## Ethernet

### Key commercial data

package_quantity	1
GTIN	4046356097383

### Technical data

#### Dimensions

External diameter	4 mm ... 8 mm
Stripping length of the sheath	35 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP67

#### General

Rated current at 40°C	1.75 A
Rated voltage	60 V
Number of positions	4
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	D - data
Standards/regulations	M12 connector IEC 61076-2-101
Signal type/category	Ethernet CAT5 (IEC 11801:2002)
Signal type/category	Ethernet CAT5e (TIA 568B:2001)
Status display	No
Surge voltage category	II
Pollution degree	3

# Bus system connector - SACC-M12MSD-4Q SH - 1543223

## Technical data

### General

<b>Connection method</b>	Insulation displacement connection
<b>Conductor cross section</b>	0.14 mm <sup>2</sup> ... 0.34 mm <sup>2</sup>
<b>AWG conductor cross section</b>	26 ... 22
<b>Frequency of connections between conductors of the same cross section</b>	≤ 10
<b>Insertion/withdrawal cycles</b>	≥ 100
<b>Torque</b>	0.4 Nm (M12 knurl)

### Material

<b>Inflammability class according to UL 94</b>	V0
<b>Contact material</b>	CuSn
<b>Contact surface material</b>	Ni/Au
<b>Contact carrier material</b>	PA 66
<b>Material of grip body</b>	Zinc die-cast, nickel-plated
<b>Material, knurls</b>	Nickel-plated brass
<b>Sealing material</b>	Neoprene

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27250313
<b>eCl@ss 4.1</b>	27250313
<b>eCl@ss 5.0</b>	27143423
<b>eCl@ss 5.1</b>	27143423
<b>eCl@ss 6.0</b>	27143423
<b>eCl@ss 7.0</b>	27449001
<b>eCl@ss 8.0</b>	27449001

### ETIM

<b>ETIM 3.0</b>	EC002062
<b>ETIM 4.0</b>	EC002062
<b>ETIM 5.0</b>	EC002062

### UNSPSC

<b>UNSPSC 6.01</b>	31251501
<b>UNSPSC 7.0901</b>	31251501
<b>UNSPSC 11</b>	31251501
<b>UNSPSC 12.01</b>	31251501
<b>UNSPSC 13.2</b>	31251501


## approvals

GOST /

# Bus system connector - SACC-M12MSD-4Q SH - 1543223

approvals

Approval details



accessories

## Torque tool

TSD 04 SAC - 1208429



TSD-M 1,2NM - 1212224



## Screwdriver tools

SACC BIT M12-D20 - 1208445



TSD-M SAC-BIT ADAPTER - 1212600



## Protective cap

## Bus system connector - SACC-M12MSD-4Q SH - 1543223

### accessories

PROT-M12 FS-PA-CHAIN - 1430873



---

### Data cable by the meter

VS-OE-OE-93E/... - 1417320



---

### Stripping tool

WIREFOX-D 40 - 1212161



---

### accessories

MICROFOX SC - 1205862




---

### Drawings


# Bus system connector - SACC-M12MSD-4Q SH - 1543223

Dimensioned drawing



Plug, M12 x 1, straight, shielded

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

