

Panel mounting frames - VS-V1-F-RJ45-MNNA-1-C-S-JI-S - 1419185

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



RJ45 mounting frame, IP67, for bayonet interlocking, metal, with contact insert for cable connection, for round mounting cutout, with seal, without mounting screws



Key commercial data

package_quantity	1
GTIN	4046356540384

Technical data

Mechanical characteristics

Number of positions	8
Number of slots	1
Insertion/withdrawal cycles	750
Connection cross section AWG	26 ... 22 (stranded)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Degree of protection	IP67

Material data

Inflammability class according to UL 94	V0
Housing material	Zinc die-cast
Seal material	NBR

Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423

Panel mounting frames - VS-V1-F-RJ45-MNNA-1-C-S-JI-S - 1419185

classifications

eCl@ss

eCl@ss 5.1	27143423
eCl@ss 6.0	27261207
eCl@ss 7.0	27440210
eCl@ss 8.0	27440210

ETIM

ETIM 3.0	EC000376
ETIM 4.0	EC002310
ETIM 5.0	EC002310

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing

