

Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 4-position, PUR, orange RAL 2003, Plug straight M12, A-coded, on Socket straight M12, A-coded, Cable length: 5 m

As shown in the illustration but with an orange conductor

Key commercial data

package_quantity	1
GTIN	4046356128810

Technical data

Dimensions

Length of cable	5 m
------------------------	-----

Ambient conditions

Degree of protection	IP65
Degree of protection	IP67
Degree of protection	IP68

General

Rated current at 40°C	4 A
Rated voltage	250 V
Number of positions	4
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Status display	No
Surge voltage category	II
Pollution degree	3
Insertion/withdrawal cycles	≥ 100

Material

Inflammability class according to UL 94	HB
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF

Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660

Technical data

Material

Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

Cable

Cable type	PUR irradiated halogen-free orange
Cable abbreviation	D12YSL11X-OB
Conductor cross section	0.34 mm ²
AWG signal line	22
Conductor structure signal line	19x 0.15 mm
Wire colors	brown, white, blue, black
Overall twist	4 wires, twisted
Length of twist, overall twist	27 mm
External sheath, color	orange RAL 2003
External cable diameter	5.20 mm
Smallest bending radius, fixed installation	min. 15 mm
Smallest bending radius, movable installation	min. 30 mm
Number of bending cycles	5000000
Bending radius	52 mm
Traversing path	10 m
Traversing rate	3 m/s
Outer sheath, material	PUR
Material conductor insulation	PE
Conductor material	Bare Cu litz wires
Conductor resistance	max. 57 Ω/km
Nominal voltage, cable	320 V
Test voltage, cable	2500 V

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 3.0	EC001855
-----------------	----------

Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660

classifications

ETIM

ETIM 4.0	EC001855
ETIM 5.0	EC001855

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

UL Listed / cUL Listed / cULus Listed /

Approval details

UL Listed	
Nominal voltage UN	300 V
Nominal current IN	4 A
mm ² /AWG/kcmil	


cUL Listed	
Nominal voltage UN	300 V
Nominal current IN	4 A
mm ² /AWG/kcmil	

cULus Listed	
---------------------	--

Drawings


Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660

Dimensioned drawing



M12 x 1 plug, straight


Dimensioned drawing



M12 x 1 socket, straight


Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660

Circuit diagram



Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660


Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660


Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

Sensor/Actuator cable - SAC-4P-M12MS/ 5,0-150/ M12FS - 1546660

Cable cross section



PUR irradiated halogen-free orange [150]

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>