

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type connector, connector, 4-pos., M12 SPEEDCON, A-coded, rear/screw mounting with M12 thread, with polarity protection, with angled solder connection



Key commercial data

package_quantity	10
GTIN	4046356438650

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	250 V
Number of positions	4
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder pins
Mounting type	Rear mounting M12 x 1 With flat nut

Material

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002061
ETIM 5.0	EC002061

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

UL Recognized /


Approval details

UL Recognized 	
Nominal voltage UN	250 V
Nominal current IN	4 A
mm²/AWG/kcmil	26-20

Drawings

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589


Drilling diagram



Drilling diagram

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589


Dimensioned drawing



M12 flush-type connector, connector, side view

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589


Dimensioned drawing



M12 flush-type connector, connector, front view

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589


Dimensioned drawing



M12 flush-type connector, plug, contact carrier, side view

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589


Dimensioned drawing



M12 flush-type connector, plug, contact carrier, front view

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589


Dimensioned drawing



Locked area on the PCB


Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589

Dimensioned drawing



Optionally with O-ring (green) for tight seal when plugged in.- the axial mating force of 80 N per connector may not be exceeded when using with assembled O-ring!- Avoid radial forces!


Dimensioned drawing



Panel cutout, view from front in case of horizontal PCB (2). The 3rd flat area is optional (1).

Flush-type connector - SACC-DSIV-MS-4CON-L90 SCO - 1436589

Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>