

## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 4-position, PUR halogen-free, Black-gray RAL 7021, Free cable end, on Socket straight M12, A-coded, Cable length: 15 m

### Key commercial data

package_quantity	1
GTIN	4017918825638

### Technical data

#### Dimensions

Length of cable	15 m
Stripping length of the free conductor end	50 mm

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
Degree of protection	IP65
Degree of protection	IP67
Degree of protection	IP68

#### General

Rated current at 40°C	4 A
Rated voltage	250 V
Number of positions	4
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Status display	No
Surge voltage category	II
Pollution degree	3
Insertion/withdrawal cycles	≥ 100

#### Material

Inflammability class according to UL 94	HB
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF

## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

### Technical data

#### Material

<b>Material of grip body</b>	TPU, hardly inflammable, self-extinguishing
<b>Material, knurls</b>	Zinc die-cast, nickel-plated
<b>Sealing material</b>	NBR

#### Cable

<b>Cable type</b>	PUR halogen-free black
<b>Cable type (abbreviation)</b>	PUR
<b>Cable abbreviation</b>	Li9Y11Y-HF
<b>UL AWM style</b>	20549 / 10493 (80°C/300 V)
<b>Conductor cross section</b>	4x 0.34 mm <sup>2</sup>
<b>AWG signal line</b>	22
<b>Conductor structure signal line</b>	42x 0.10 mm
<b>Core diameter including insulation</b>	1.27 mm ±0.02 mm
<b>Thickness, insulation</b>	≥ 0.21 mm
<b>Wire colors</b>	brown, white, blue, black
<b>Overall twist</b>	4 wires, twisted
<b>External sheath, color</b>	Black-gray RAL 7021
<b>Outer sheath thickness</b>	approx. 0.8 mm
<b>External cable diameter D</b>	4.7 mm ±0.15 mm
<b>Minimum bending radius, fixed installation</b>	5 x D
<b>Minimum bending radius, flexible installation</b>	10 x D
<b>Number of bending cycles</b>	4000000
<b>Minimum bending radius, drag chain applications</b>	10 x D
<b>Traversing path</b>	10 m
<b>Traversing rate</b>	3 m/s
<b>Acceleration</b>	10 m/s <sup>2</sup>
<b>Cable weight</b>	30 kg/km
<b>Outer sheath, material</b>	PUR
<b>Material conductor insulation</b>	PP
<b>Conductor material</b>	Bare Cu litz wires
<b>Insulation resistance</b>	≥ 1 GΩ*km
<b>Conductor resistance</b>	≤ 58 Ω/km
<b>Nominal voltage, cable</b>	≤ 300 V
<b>Test voltage, cable</b>	≥ 3000 V
<b>Special properties</b>	Flexible cable conduit capable
<b>Special properties</b>	Silicone-free
<b>Special properties</b>	Free of substances which would hinder coating with paint or varnish
<b>Special properties</b>	Flexible
<b>Flame resistance</b>	in accordance with DIN UL-Style 20549
<b>Flame resistance</b>	in accordance with FT1 as per UL 758
<b>Halogen-free</b>	in accordance with DIN VDE 0472 part 815

# Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

## Technical data

### Cable

<b>Halogen-free</b>	in accordance with DIN EN 50267-2-1
<b>Resistance to oil</b>	in accordance with DIN EN 60811-2-1
<b>Other resistance</b>	Highly resistant to acids, alkaline solutions and solvents
<b>Other resistance</b>	hydrolysis and microbe resistant
<b>Other resistance</b>	partly UV-resistant in accordance with DIN EN ISO 4892-2-A
<b>Other resistance</b>	Low adhesion
<b>Other resistance</b>	abrasion-resistant
<b>Ambient temperature (operation)</b>	-40 °C ... 80 °C (cable, fixed installation)
<b>Ambient temperature (operation)</b>	-25 °C ... 80 °C (cable, flexible installation)

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 2.0</b>	EC000830
<b>ETIM 3.0</b>	EC001855
<b>ETIM 4.0</b>	EC001855
<b>ETIM 5.0</b>	EC001855


### UNSPSC

<b>UNSPSC 6.01</b>	31251501
<b>UNSPSC 7.0901</b>	31251501
<b>UNSPSC 11</b>	31251501
<b>UNSPSC 12.01</b>	31251501
<b>UNSPSC 13.2</b>	31251501

## approvals

UL Listed / cUL Listed / cULus Listed /

### Approval details


---

# Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

## approvals

Nominal voltage UN	300 V
Nominal current IN	4 A
mm <sup>2</sup> /AWG/kcmil	

cUL Listed	
Nominal voltage UN	300 V
Nominal current IN	4 A
mm <sup>2</sup> /AWG/kcmil	

cULus Listed	
--------------	--

## accessories

### Conductor marking

PABA WH/15 - 1013151



PABA YE/15 - 1013698



PABA RD/15 - 1013944



### Marker carrier cable

## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

### accessories

PATG 2/15 - 1013038



PATG 3/15 - 1013041



PATG 4/15 - 1013054



### Marker pen

B-STIFT - 1051993



### Cutting tools

CUTFOX-S VDE - 1212207



### Stripping tool

## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

### accessories

WIREFOX SAC - 1212623



WIREFOX 10 - 1212150



### Protective cap

PROT-M12 MS-PA-CHAIN - 1430899



### Safety locking

SAC-M12-EXCLIP-F - 1558991



### Torque tool

TSD 04 SAC - 1208429



## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

### accessories

TSD-M 1,2NM - 1212224



---

### Screwdriver tools

TSD-M SAC-BIT ADAPTER - 1212600



---

SAC BIT M12-D15 - 1208432



---

### accessories


WIREFOX SAC-1 - 1212757

---

### Drawings


## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

Dimensioned drawing



M12 x 1 socket, straight

Circuit diagram




Contact assignment of the M12 socket



## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730


Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

## Sensor/Actuator cable - SAC-4P-15,0-PUR/M12FS - 1502730

Cable cross section



PUR halogen-free black [PUR]

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>