

Flush-type connector - SACC-DSIV-M12FSB-5CON-L180-SI - 1528196

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator flush-type socket, 5-pos., M12, B-coded, rear/screw mounting with Pg9 thread, with straight solder connection

Key commercial data

package_quantity	10
GTIN	4046356023177

Technical data

Ambient conditions

Degree of protection	IP67
----------------------	------

General

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	5
Contact resistance	$\leq 0.003 \Omega$
Insulation resistance	$\geq 1 T\Omega$
Coding	B - inverse
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Solder pins

Material

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PBT
Material, knurls	Nickel-plated brass
Sealing material	NBR

classifications

eCl@ss

Flush-type connector - SACC-DSIV-M12FSB-5CON-L180-SI - 1528196

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

ETIM

ETIM 2.0	EC001297
ETIM 3.0	EC002061
ETIM 4.0	EC002062
ETIM 5.0	EC002062


UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Drawings

Flush-type connector - SACC-DSIV-M12FSB-5CON-L180-SI - 1528196

Schematic diagram



Pin assignment M12 socket, 5-pos., B-coded, female side

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>