

Pressure screw set - HC-DS-PG16-E - 1676899

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pg pressure screw set, standard version; for housing with Pg16 support; consisting of pressure screw, notched seal and 2 washers

Key commercial data

package_quantity	10
GTIN	4017918129514

Technical data

Dimensions

Wrench size, union nut	22 mm
External cable diameter	7.5 mm ... 15 mm
Conductor sealing range	7.50 mm ... 15.00 mm

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material, pressure screw	Nickel-plated brass
Cable seal material	Perbunan
Thread type on connection side	Pg16

classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441

Pressure screw set - HC-DS-PG16-E - 1676899

classifications

ETIM

ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

approvals

GOST /

Approval details

 GOST

Drawings

Pressure screw set - HC-DS-PG16-E - 1676899

Dimensioned drawing

