

Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 3-position, PUR, Black RAL 9005, Free cable end, on Socket straight M5, A-coded, Cable length: 3 m

Product Features

- ✓ Easy and safe: 100% electrically tested plug-in components
- ✓ Signal transmission in a confined space – with our M5 connectors

Key commercial data

package_quantity	1
GTIN	4046356024235

Technical data

Dimensions

Length of cable	3 m
-----------------	-----

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C (Plug / socket)
Degree of protection	IP65
Degree of protection	IP67
Degree of protection	IP68

General

Rated current at 40°C	1 A
Rated voltage	125 V
Number of positions	3
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 10 GΩ
Coding	A - standard
Standards/regulations	M5 connector IEC 61076-2-105
Status display	No
Protective circuit/component	Unwired
Surge voltage category	II
Pollution degree	3
Test voltage	1750 V
Insertion/withdrawal cycles	≥ 100

Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

Technical data

Material

Contact material	CuSn
Contact surface material	Au
Contact carrier material	PUR
Material of grip body	PUR
Material, knurls	Nickel-plated brass
Sealing material	NBR

Cable

Cable type	PUR/PVC black
Conductor cross section	3x 0.14 mm ² (signal line)
AWG signal line	26
Conductor structure signal line	18x 0.10 mm
Core diameter including insulation	1.1 mm
Wire colors	brown, blue, black
Overall twist	3 wires, twisted
External sheath, color	Black RAL 9005
External cable diameter D	3 mm ± 0.2 mm
Smallest bending radius, fixed installation	8 mm
Smallest bending radius, movable installation	15 mm
Cable weight	12.9 kg/km
Outer sheath, material	PUR
Material conductor insulation	PVC
Conductor material	Bare Cu litz wires
Insulation resistance	100 MΩ*km
Conductor resistance	148 Ω/km
Nominal voltage, cable	250 V
Test voltage, cable	800 V _{rms}
Ambient temperature (operation)	-15 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation)	-5 °C ... 80 °C (cable, flexible installation)

classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000830
----------	----------

Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

classifications

ETIM

ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

approvals

GOST /

Approval details

GOST 
--

accessories

Conductor marking

PABA WH/15 - 1013151



PABA YE/15 - 1013698



Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

accessories

PABA RD/15 - 1013944



Marker carrier cable

PATG 2/15 - 1013038



PATG 3/15 - 1013041



PATG 4/15 - 1013054



Marker pen

B-STIFT - 1051993



Cutting tools

Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

accessories

CUTFOX-S VDE - 1212207



Stripping tool

WIREFOX SAC - 1212623



WIREFOX 10 - 1212150




accessories

WIREFOX SAC-1 - 1212757

Drawings


Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

Dimensioned drawing



Socket M5 x 0.5, straight


Circuit diagram



Contact assignment of the M5 socket

Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430


Schematic diagram



Socket M5, 3-pos.

Sensor/Actuator cable - SAC-3P- 3,0-PUR/M5FS - 1530430

Cable cross section



PUR/PVC black [350]

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>