

# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/Actuator cable, 4-position, PUR, orange RAL 2003, Plug straight M12, A-coded, on Socket straight M12, A-coded, Cable length: 0.6 m

As shown in the illustration but with an orange conductor

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356128766

## Technical data

### Dimensions

<b>Length of cable</b>	0.6 m
------------------------	-------

### Ambient conditions

<b>Degree of protection</b>	IP65
<b>Degree of protection</b>	IP67
<b>Degree of protection</b>	IP68

### General

<b>Rated current at 40°C</b>	4 A
<b>Rated voltage</b>	250 V
<b>Number of positions</b>	4
<b>Contact resistance</b>	≤ 5 mΩ
<b>Insulation resistance</b>	≥ 100 MΩ
<b>Coding</b>	A - standard
<b>Status display</b>	No
<b>Surge voltage category</b>	II
<b>Pollution degree</b>	3
<b>Insertion/withdrawal cycles</b>	≥ 100

### Material

<b>Inflammability class according to UL 94</b>	HB
<b>Contact material</b>	CuSn
<b>Contact surface material</b>	Ni/Au
<b>Contact carrier material</b>	TPU GF

# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589

## Technical data

### Material

<b>Material of grip body</b>	TPU, hardly inflammable, self-extinguishing
<b>Material, knurls</b>	Zinc die-cast, nickel-plated
<b>Sealing material</b>	NBR

### Cable

<b>Cable type</b>	PUR irradiated halogen-free orange
<b>Cable abbreviation</b>	D12YSL11X-OB
<b>Conductor cross section</b>	0.34 mm <sup>2</sup>
<b>AWG signal line</b>	22
<b>Conductor structure signal line</b>	19x 0.15 mm
<b>Wire colors</b>	brown, white, blue, black
<b>Overall twist</b>	4 wires, twisted
<b>Length of twist, overall twist</b>	27 mm
<b>External sheath, color</b>	orange RAL 2003
<b>External cable diameter</b>	5.20 mm
<b>Smallest bending radius, fixed installation</b>	min. 15 mm
<b>Smallest bending radius, movable installation</b>	min. 30 mm
<b>Number of bending cycles</b>	5000000
<b>Bending radius</b>	52 mm
<b>Traversing path</b>	10 m
<b>Traversing rate</b>	3 m/s
<b>Outer sheath, material</b>	PUR
<b>Material conductor insulation</b>	PE
<b>Conductor material</b>	Bare Cu litz wires
<b>Conductor resistance</b>	max. 57 Ω/km
<b>Nominal voltage, cable</b>	320 V
<b>Test voltage, cable</b>	2500 V

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 3.0</b>	EC001855
-----------------	----------

# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589

## classifications

### ETIM

<b>ETIM 4.0</b>	EC001855
<b>ETIM 5.0</b>	EC001855


### UNSPSC


<b>UNSPSC 6.01</b>	31251501
<b>UNSPSC 7.0901</b>	31251501
<b>UNSPSC 11</b>	31251501
<b>UNSPSC 12.01</b>	31251501
<b>UNSPSC 13.2</b>	31251501


## approvals

UL Listed / cUL Listed / cULus Listed /

### Approval details

<b>UL Listed</b> 	
Nominal voltage UN	300 V
Nominal current IN	4 A
mm <sup>2</sup> /AWG/kcmil	


<b>cUL Listed</b> 	
Nominal voltage UN	300 V
Nominal current IN	4 A
mm <sup>2</sup> /AWG/kcmil	

<b>cULus Listed</b> 	
---	--

## Drawings


# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589

Dimensioned drawing



M12 x 1 plug, straight


Dimensioned drawing



M12 x 1 socket, straight


# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589

Circuit diagram



# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589


Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

# Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589


Schematic diagram



Pin assignment M12 socket, 4-pos., A-coded, view female side

## Sensor/Actuator cable - SAC-4P-M12MS/ 0,6-150/ M12FS - 1546589

Cable cross section



PUR irradiated halogen-free orange [150]

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>