

Device connector, rear mounting - ST-17S1N8AH100S - 1613543

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Device connector, rear mounting, straight, SPEEDCON locking, M17, Number of positions: 17, Type of contact: Socket, Crimp connection, Axial O-ring, Central fixing, shielded: Yes

Key commercial data

package_quantity	1
GTIN	4046356400947

Technical data

General

Note	Order information Order crimp contacts Ø 0.6 mm separately
Type of locking	SPEEDCON locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Socket
Number of positions	17
Contact diameter of power contacts	0.6 mm
Nominal current per power contact at 25°C	3.6 A
Mounting type	Central fixing

Ambient conditions

Ambient temperature	-20 °C ... 125 °C
Degree of protection	IP67

Material

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA 66
Gasket and O-ring material	FPM

Specifications according to DIN EN 61984:2001

Installation height max.	3000 m
Nominal / operating voltage of power contacts	60 V
Rated surge voltage of power contacts	1.5 kV
Surge voltage category of power contacts	II
Pollution degree of power contacts	3

Device connector, rear mounting - ST-17S1N8AH100S - 1613543

Technical data

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002635

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized 	
Nominal voltage UN	60 V
Nominal current IN	1 A
mm²/AWG/kcmil	0.14-0.6

cUL Recognized 	
Nominal voltage UN	60 V
Nominal current IN	1 A

Device connector, rear mounting - ST-17S1N8AH100S - 1613543

approvals

mm²/AWG/kcmil	0.14-0.6



accessories

Crimp contact

ST-06KS010 - 1607580



ST-06KS020 - 1607581



ST-06KS030 - 1607582



Protective cover

ST-Z0006 - 1607776



Mounting material

Device connector, rear mounting - ST-17S1N8AH100S - 1613543 accessories

ST-Z0019 - 1620621



ST-Z0020 - 1620622



ST-Z0021 - 1620623




ST-Z0001 - 1607770




Drawings

Device connector, rear mounting - ST-17S1N8AH100S - 1613543

Diagram




Diagram




Device connector, rear mounting - ST-17S1N8AH100S - 1613543

Dimensioned drawing



Device connector, rear mounting - ST-17S1N8AH100S - 1613543


Dimensioned drawing



Installation dimensions: mounting with anti-rotation protection and locking nut

Device connector, rear mounting - ST-17S1N8AH100S - 1613543

Dimensioned drawing



Installation dimensions: mounting with thread

Device connector, rear mounting - ST-17S1N8AH100S - 1613543

Schematic diagram

