

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator terminal block, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Connection type: Screw connection, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

The figure shows the version
VIOK 1,5-LA 24RD/O-MO

Key commercial data

package_quantity	50
GTIN	4017918062231

Technical data

General

Number of levels	4
Number of connections	5
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V2

General

Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I _N	24 A
Nominal voltage U _N	250 V (the voltage is determined by the light indicator.)
Open side panel	nein

Dimensions

Width	6.2 mm
Length	62.5 mm
Height NS 35/7,5	70 mm
Height NS 35/15	77.5 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

Technical data

Connection data

Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Cross section with insertion bridge, solid max.	4 mm ²
Cross section with insertion bridge, stranded max.	2.5 mm ²
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141128
eCl@ss 7.0	27141128
eCl@ss 8.0	27141128

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

classifications

ETIM

ETIM 2.0	EC000900
ETIM 3.0	EC000900
ETIM 4.0	EC000900
ETIM 5.0	EC000900

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

Approval details

CSA 	
Nominal voltage UN	300 V
Nominal current IN	15 A
mm²/AWG/kcmil	28-14

UL Recognized 				
Usegroups	B	C	D	
Nominal voltage UN	300 V	150 V	300 V	
Nominal current IN	15 A	15 A	10 A	
mm²/AWG/kcmil	30-14	30-14	30-14	

cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	15 A	15 A	10 A
mm²/AWG/kcmil	30-14	30-14	30-14

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

approvals

cULus Recognized  US

accessories

Terminal marking

SBS 6:UNBEDRUCKT - 1007222



ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Bridge

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

EB 80- DIK BU - 2715940



EB 10- DIK RD - 2716774



EB 10- DIK BU - 2716680



EB 80- DIK RD - 2715953



EB 10- DIK GY - 2715937



Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

EB 80- DIK WH - 2715788



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

accessories

E/NS 35 N - 0800886



E/UK - 1201442




E/UK 1 - 1201413



Drawings

Sensor/actuator terminal block - VIOK 1,5-LA 24GN/MU-O - 2718141

Circuit diagram



1 = fixed bridge2 = insertion bridge

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>