

Interface module - FLKMS-D50 SUB/B - 2281775

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and D-Subminiature socket strip, for mounting on NS 35/7.5 or NS 32, 50-pos.

The illustration shows version FLKMS-D37 SUB/S (1-37)



Key commercial data

package_quantity	5
GTIN	4017918055028

Technical data

Dimensions

Width	101.5 mm
Height	77 mm
Depth	72 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 45 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	125 V AC/DC
Max. current carrying capacity per branch	2 A
Number of positions	50
Test voltage	800 V AC (50 Hz, 1 min.)
Mounting position	Any
Standards/regulations	IEC 60664
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN

Interface module - FLKMS-D50 SUB/B - 2281775

Technical data

Connection data for connection 1

Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M3

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

approvals

GOST /

Approval details



Interface module - FLKMS-D50 SUB/B - 2281775

accessories

System cable

CABLE-D50SUB/B/S/ 50/KONFEK/S - 2302269



CABLE-D50SUB/B/S/100/KONFEK/S - 2302272



CABLE-D50SUB/B/S/150/KONFEK/S - 2302285



CABLE-D50SUB/B/S/200/KONFEK/S - 2302298



CABLE-D50SUB/B/S/300/KONFEK/S - 2302308



Interface module - FLKMS-D50 SUB/B - 2281775

accessories

CABLE-D50SUB/B/S/400/KONFEK/S - 2302311



CABLE-D50SUB/B/S/600/KONFEK/S - 2302324



CABLE D-SUB-S/.../.../... - 2302340



CABLE D-SUB-S-S-S/.../.../... - 2302434



CABLE-D-50SUB/M/OE/0,25/S/0,5M - 2926645



CABLE-D-50SUB/M/OE/0,25/S/1,0M - 2926658



Interface module - FLKMS-D50 SUB/B - 2281775

accessories

CABLE-D-50SUB/M/OE/0,25/S/1,5M - 2926661



CABLE-D-50SUB/M/OE/0,25/S/2,0M - 2926674



CABLE-D-50SUB/M/OE/0,25/S/3,0M - 2926687



CABLE-D-50SUB/M/OE/0,25/S/4,0M - 2926690



CABLE-D-50SUB/M/OE/0,25/S/6,0M - 2926700



Interface module - FLKMS-D50 SUB/B - 2281775

accessories

CABLE-D-50SUB-M-OE-0,25-S/... - 2900913



Drawings

Schematic diagram

