

Front adapters - FLKM S115/S400/SO155 - 2307248

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



The FLKM S115/S400/SO adapter links a SIMATIC® S5 plug directly with the basic SIMATIC® S7 400 card. Conversion: 6ES5 420-7LA11 / 6ES5 430-7LA11 on 6ES7-421-1BL01-0AA0 or 6ES5 441-7LA11 / 6ES5 451-7LA11 on 6ES7 422-1BL01-0AA0

Key commercial data

package_quantity	1
GTIN	4017918985554

Technical data

General

Nominal voltage U_N	24 V AC/DC
Max. permissible current	4 A (per path)
Max. permissible current	4 A (per connection, supply via separate power supply)
Connection type, connector	SIEMENS S5-115 U pin strip
Mounting position	Vertical
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Supported controller

Control	SIEMENS S5-115 U
- suitable I/O card	6ES5 420-7LA11
- suitable I/O card	6ES5 430-7LA11
- suitable I/O card	6ES5 441-7LA11
- suitable I/O card	6ES5 451-7LA11

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313

Front adapters - FLKM S115/S400/SO155 - 2307248

classifications

eCl@ss

eCl@ss 6.0	27249205
eCl@ss 7.0	27249205
eCl@ss 8.0	27249205

ETIM


ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Drawings

Circuit diagram



Connection scheme: FLKM S115/S400/SO155