

Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Fuse terminal block for cartridge fuse insert, cross section: 0.5-10 mm², AWG: 20-8, width: 12.2 mm, color: Black

Key commercial data

package_quantity	25
GTIN	4046356052818

Technical data

General

Number of levels	1
Number of connections	2
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

General

Fuse	G / 5 x 20
Fuse type	Glass
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-3
Nominal current I _N	10 A
Nominal voltage U _N	500 V
LED voltage range	110 V AC ... 250 V AC
LED current range	0.5 mA ... 2.5 mA
Open side panel	nein

Dimensions

Width	12.2 mm
Length	71.5 mm
Height NS 35/7,5	51.3 mm

Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

Technical data

Dimensions

Height NS 35/15	58.8 mm
-----------------	---------

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	6 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	8
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	6 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	6 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm ²
Connection method	Leg spring connection
Stripping length	12 mm
Internal cylindrical gage	A5

classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

UNSPSC

UNSPSC 6.01	30211825
-------------	----------

Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

classifications

UNSPSC

UNSPSC 7.0901	39121422
UNSPSC 11	39121422
UNSPSC 12.01	39121422
UNSPSC 13.2	39121422

approvals

UL Recognized / KEMA-KEUR / cUL Recognized / IECCE CB Scheme / GOST / GOST / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	10 A	10 A
mm²/AWG/kcmil	20-8	20-8

KEMA-KEUR 	
Nominal voltage UN	250 V
Nominal current IN	10 A
mm²/AWG/kcmil	0.5-6

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	10 A	10 A
mm²/AWG/kcmil	20-8	20-8

IECEE CB Scheme 	
Nominal voltage UN	250 V
Nominal current IN	10 A

Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

approvals

mm²/AWG/kcmil	0.5-6



accessories

Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Bridge

FBS 2-6 - 3030336



FBS 3-6 - 3030242



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

FBS 4-6 - 3030255



FBS 5-6 - 3030349



FBS 10-6 - 3030271



FBS 20-6 - 3030365



RB ST (2,5/4)-1,5 - 3038943



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

RB UT 35-ST(2,5/4) - 3047280



RB UT 16-ST(2,5/4) - 3047099



RB UT 10-ST(2,5/4) - 3047086



RB UT 6-ST(2,5/4) - 3047264



RB ST 35-(2,5/4) - 3030899



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

RB ST 16-(2,5/4) - 3030886



RB ST 10-(2,5/4) - 3030873



RB ST 6-(2,5/4) - 3030860



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Test plug terminal block

PS-6 - 3030996



PS-6/2,3MM RD - 3038736



PAI-4-FIX-5/6 BU - 3035975



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



End cover

DP PS-6 - 3036738



End block

CLIPFIX 35 - 3022218



Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

accessories

CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442




E/UK 1 - 1201413



Drawings

Fuse modular terminal block - DT 6/2,5-DREHSILA 250
(5X20) - 3034264


Application drawing



Fuse terminal blocks in interconnected arrangement, block consisting of 5 fuse terminal blocks

Fuse modular terminal block - DT 6/2,5-DREHSILA 250 (5X20) - 3034264

Application drawing



Fuse terminal block in single arrangement, block consisting of one fuse terminal block and 4 feed-through terminal blocks

Circuit diagram

