

Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection type: Screw connection, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Nominal current: 26 A, Nominal voltage: 400 V, Length: 80 mm, Width: 6 mm, Color: gray, Assembly: NS 35/7,5, NS 35/15, NS 32

Product Features

- Closed housing of double-level terminal blocks
- Space-saving design just 6.2 mm wide

Key commercial data

package_quantity	50
GTIN	4017918074180

Technical data

General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V2

General

Maximum load current	26 A (with 4 mm ² conductor cross section)
Maximum load current	12 A (with 4 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I_N	26 A
Nominal voltage U_N	400 V
Open side panel	nein

Dimensions

Width	6 mm
Length	80 mm
Height NS 35/7,5	68 mm

Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

Technical data

Dimensions

Height NS 35/15	76 mm
Height NS 32	73 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm ²
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120

Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

classifications

eCl@ss

eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / cUL Recognized / BV / PRS / cULus Recognized /

Approval details

CSA	
Nominal voltage UN	300 V
Nominal current IN	15 A
mm ² /AWG/kcmil	22-12

UL Recognized		
Usegroups	B	C
Nominal voltage UN	250 V	300 V
Nominal current IN		
mm ² /AWG/kcmil	26-12	26-12

cUL Recognized		
Usegroups	B	C
Nominal voltage UN	250 V	300 V

Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

approvals

Usegroups	B	C
Nominal current I _N		
mm ² /AWG/kcmil	26-12	26-12

BV

PRS

cULus Recognized  US

accessories

Terminal marking

SBS 6:UNBEDRUCKT - 1007222



ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

Insulating sleeve

IS-K 4 - 1302338



ISSBI 10- 6 - 0301505



Bridge

FBI 10- 6 - 0203250



FBI 100- 6 - 0201650



FBI 20- 6 - 0201867



Mounting rail

Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

ZB 6 CUS - 0824992



Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Feed-through terminal block - UKK 5-MTKD-P/P - 2800017

accessories

E/UK - 1201442



E/UK 1 - 1201413



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>