

Component connector - ST-BE - 2802316

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component connector, to connect 2-pos. components to the basic terminal block, to be secured with screw-type clamping units, 19 mm high, max. 16 A

Key commercial data

package_quantity	10
GTIN	4017918074401

Technical data

General

Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Nominal current I _N	16 A
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	125 °C

Dimensions

Length	42 mm
Height	19 mm

Connection data

Stripping length	7 mm
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141149
eCl@ss 7.0	27141149

Component connector - ST-BE - 2802316

classifications

eCl@ss

eCl@ss 8.0	27141149
------------	----------

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002018
ETIM 5.0	EC002018

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

UL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	10 A
mm²/AWG/kcmil	30-14

cUL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	10 A
mm²/AWG/kcmil	30-14

GOST 	
---	--

Component connector - ST-BE - 2802316

approvals



cULus Recognized  US

accessories

Documentation

ST-IL - 3039900



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>