

Special function module - EEM-MEMO-MA600 - 2901370

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Storage module for intermediate storage of values (512 kB) for EEM-MA600

Product Features

- ✓ Stores the last ten alarms together with the time and date
- ✓ Stores the real and reactive power, e.g., for 31 days with a ten-minute synchronization pulse

Key commercial data

package_quantity	1
GTIN	4046356585798

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	22.5 mm
Height	65 mm
Depth	48 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 55 °C (14 °F to 131 °F)
Ambient temperature (storage/transport)	-20 °C ... 85 °C (-4 °F ... 185 °F)
Max. permissible relative humidity (operation)	≤ 95 %
Max. salt spray content	≤ 2.5 %

Input data

Description of the input	Optocoupler input
Number	1
Voltage input signal	10 V DC ... 30 V DC
Input pulse length	≥ 1 s
Peak offstate voltage	30 V DC
Memory size	512 kByte

General

Special function module - EEM-MEMO-MA600 - 2901370

Technical data

General

Supply voltage	9 V (via EEM-MA600)
Color	black
Conformance	CE-compliant
Rated insulation voltage at mains voltage < 300 V AC (L/N)	III
Rated insulation voltage at mains voltage > 300 V AC - 600 V AC (L/N)	II
Test voltage	3.5 kV AC (50 Hz, 1 min.)

Connection data

Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	14
Connection method	COMBICON plug-in screw terminal block
Stripping length	6 mm
Tightening torque	0.4 Nm

classifications

eCl@ss

eCl@ss 4.0	27210902
eCl@ss 4.1	27371105
eCl@ss 5.0	27371801
eCl@ss 5.1	27371801
eCl@ss 6.0	27371801
eCl@ss 7.0	27371801
eCl@ss 8.0	27371801

ETIM

ETIM 3.0	EC001505
ETIM 4.0	EC000192
ETIM 5.0	EC000192

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121535

Special function module - EEM-MEMO-MA600 - 2901370

approvals

UL Listed / cUL Listed / cULus Listed /

Approval details

UL Listed 

cUL Listed 

cULus Listed 

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>