

Special function module - EEM-2DIO-MA600 - 2901371

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Special functional module with two digital inputs and outputs for EEM-MA600

Product Features

- ✓ Two digital inputs and outputs
- ✓ Configurable threshold values

Key commercial data

package_quantity	1
GTIN	4046356585019

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	22.5 mm
Height	65 mm
Depth	48 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-10 °C ... 55 °C (14 °F to 131 °F)
Ambient temperature (storage/transport)	-20 °C ... 85 °C (-4 °F ... 185 °F)
Max. permissible relative humidity (operation)	≤ 95 %
Max. salt spray content	≤ 2.5 %

Input data

Description of the input	Optocoupler input
Number	2
Voltage input signal	10 V DC ... 30 V DC
Input pulse length	10 ms
Peak offstate voltage	30 V DC

Output data

Output description	Relay output
--------------------	--------------

Special function module - EEM-2DIO-MA600 - 2901371

Technical data

Output data

Number	2
Maximum switching voltage	250 V AC/DC
Switching capacity	1150 VA (5 A / 230 V AC)
Electrical service life	1 x 10 ⁶ (Switching cycles with ohmic load)

Interfaces

Connection method	Pluggable screw terminal block
-------------------	--------------------------------

General

Supply voltage	9 V (via EEM-MA600)
Color	black
Conformance	CE-compliant
Rated insulation voltage at mains voltage < 300 V AC (L/N)	III
Rated insulation voltage at mains voltage > 300 V AC - 600 V AC (L/N)	II
Test voltage	3.5 kV AC (50 Hz, 1 min.)

Connection data

Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	14
Connection method	COMBICON plug-in screw terminal block
Stripping length	6 mm
Tightening torque	0.4 Nm

classifications

eCl@ss

eCl@ss 4.0	27210902
eCl@ss 4.1	27210902
eCl@ss 5.0	27210902
eCl@ss 5.1	27371801
eCl@ss 6.0	27371801
eCl@ss 7.0	27371801
eCl@ss 8.0	27371801

ETIM

ETIM 3.0	EC001505
ETIM 4.0	EC001438
ETIM 5.0	EC001438

UNSPSC

Special function module - EEM-2DIO-MA600 - 2901371

classifications

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121535

approvals

UL Listed / cUL Listed / UL Listed / cUL Listed / cULus Listed /

Approval details

UL Listed 

cUL Listed 





cULus Listed 

Drawings