

Foot element - UM 25/45-FEO 200 - 2959434

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Foot element, is inserted in the profile housing, limit stop with screw. Mounted at right angles to the NS 35/7.5 DIN rail

Product Features

- UM ...-SES lateral element offers options for labeling with Phoenix Contact marking material
- Fast mounting
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts
- High degree of mechanical stability by screwing the lateral elements to the profile
- The UMK-BF mounting flange enables modules to be mounted directly on the wall
- Cable fixing by means of UM ...-SEK lateral element (fixed using cable binders, not supplied as standard)

Key commercial data

package_quantity	10
GTIN	4017918117610

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501

Foot element - UM 25/45-FEO 200 - 2959434

classifications

UNSPSC

UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals


UL Recognized /

Approval details




Drawings

Dimensioned drawing



Foot element - UM 25/45-FEO 200 - 2959434

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>