

Feed-through terminal block - UK 3 N BU - 3001514

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Width: 5.2 mm, Color: blue, Mounting type: NS 32, NS 35/15, NS 35/7,5

Product Features

- Universal foot which can be used on NS 35... and NS 32... DIN rails
- The UK universal screw terminal block series has the typical features which are decisive for practical applications
- Potential distribution via fixed bridges in the terminal center or insertion bridges in the clamping space



Key commercial data

package_quantity	50
GTIN	4017918089962

Technical data

General

Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	32 A (with 4 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	24 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	5.2 mm
-------	--------

Feed-through terminal block - UK 3 N BU - 3001514

Technical data

Dimensions

Length	42.5 mm
Height NS 35/7,5	47 mm
Height NS 35/15	54.5 mm
Height NS 32	52 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
Cross section with insertion bridge, solid max.	4 mm ²
Cross section with insertion bridge, stranded max.	2.5 mm ²
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

Feed-through terminal block - UK 3 N BU - 3001514

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC


UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / FM approved / GL / CSA / UL Recognized / KEMA-KEUR / cUL Recognized / GOST / GL / DNV / CCA / GOST / cULus Recognized /


Approval details


IECEX	
Nominal voltage UN	690 V
Nominal current IN	23 A
mm ² /AWG/kcmil	0.2-2.5


ATEX 	
Nominal voltage UN	690 V
Nominal current IN	29 A
mm ² /AWG/kcmil	0.2-4


Feed-through terminal block - UK 3 N BU - 3001514


approvals

FM approved 	
Nominal voltage UN	300 V
Nominal current IN	20 A
mm ² /AWG/kcmil	28-12

GL 	
Nominal voltage UN	690 V
Nominal current IN	23 A
mm ² /AWG/kcmil	2.5

CSA 	
Nominal voltage UN	600 V
Nominal current IN	20 A
mm ² /AWG/kcmil	28-12

UL Recognized 	
Usegroups	C
Nominal voltage UN	600 V
Nominal current IN	20 A
mm ² /AWG/kcmil	28-12

KEMA-KEUR 	
Nominal voltage UN	800 V
Nominal current IN	24 A
mm ² /AWG/kcmil	2.5

cUL Recognized 	
---	--


Feed-through terminal block - UK 3 N BU - 3001514

approvals

Nominal voltage UN	600 V
Nominal current IN	20 A
mm ² /AWG/kcmil	28-12



CCA	
Nominal voltage UN	800 V
Nominal current IN	
mm ² /AWG/kcmil	2.5



accessories

End cover

D-UK 4/10 - 3003020



D-UK 4/10 BU - 3003101



Feed-through terminal block - UK 3 N BU - 3001514

accessories

Warning label printed

WS 3- 5 - 0805357



WS 4- 5 - 0805344



WS 5- 5 - 0805331



Mounting material

ZSR - 2303608



Bridge

FB-150 METER - 0201595



Feed-through terminal block - UK 3 N BU - 3001514

accessories

FBR 80-5-EX - 3000942



FBRI 20-5 N - 3000515



FBRI 16-5 N - 3000476



FBRI 12-5 N - 3000434



FBRI 2-5 N - 3000227



FBRI 10-5 N - 2770642



Feed-through terminal block - UK 3 N BU - 3001514

accessories

FBR 10-5-EX - 2303226



FBRI 40-5 N - 3006823



EBL 3- 5 - 2303158



EBL 2- 5 - 2303145



EBL 10- 5 - 2303132



Feed-through terminal block - UK 3 N BU - 3001514

accessories

USBR 2-7 - 2303239



USBRJ 2-7 - 2305538



Cover profile

EA 5-WS - 1024085



EA 5 - 1024014



Short-circuit connector

KSS 5 - 2303543



Test plug terminal block

Feed-through terminal block - UK 3 N BU - 3001514

accessories

PS-UK 2,5 B/Z-5 - 3001226



PS-UK 2,5 B/E - 3001132



RPS - 0201647



MPS-MT - 0201744



Partition plate

TS-K - 1302215



Partition plate

Feed-through terminal block - UK 3 N BU - 3001514

accessories

ATP-UK - 3003224



Terminal marking

SBS 5:UNBEDRUCKT - 1007219



ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



Mounting rail

Feed-through terminal block - UK 3 N BU - 3001514

accessories

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - UK 3 N BU - 3001514

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Feed-through terminal block - UK 3 N BU - 3001514

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - UK 3 N BU - 3001514

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

ZB 5 CUS - 0824962



Feed-through terminal block - UK 3 N BU - 3001514

accessories

UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



Feed-through terminal block - UK 3 N BU - 3001514

accessories

MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



End block

CLIPFIX 35 - 3022218



Feed-through terminal block - UK 3 N BU - 3001514

accessories

CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Test socket

PSBJ 3/13/4 - 0201304



Feed-through terminal block - UK 3 N BU - 3001514

accessories

PSB 3/10/4 - 0601292



accessories

PS-UK 3-5/Z-5 - 3001459

FBRI 19-5 N - 3000502

FBRI 18-5 N - 3000492


FBRI 17-5 N - 3000489

Feed-through terminal block - UK 3 N BU - 3001514

accessories

FBRI 15-5 N - 3000463

FBRI 14-5 N - 3000450



FBRI 13-5 N - 3000447



FBRI 11-5 N - 3000421

Drawings

Circuit diagram

