

# Ferrule - A 0,34- 7 - 3009202

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 7 mm, Color: silver

The figure shows variant A 1-10

## Product Features

- The A 0,25.. ferrules can also be used to process 0.14 mm<sup>2</sup> conductors
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

## Key commercial data

<b>package_quantity</b>	1000
<b>GTIN</b>	4017918091712

## Technical data

### Dimensions

<b>Length (b)</b>	7 mm
<b>Sleeve length</b>	6.3 mm
<b>Inner dimension of the insulating collar (d)</b>	1.8 mm
<b>Ferrule diameter</b>	0.9 mm
<b>Sleeve wall thickness</b>	0.15 mm

### Ambient conditions

<b>Max. permanent temperature</b>	105 °C
-----------------------------------	--------

### General

<b>Note</b>	These ferrules are not included in DIN 46228-1: 1992-08
<b>Color</b>	silver
<b>Material</b>	E-CU

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060701
<b>eCl@ss 4.1</b>	27060701
<b>eCl@ss 5.0</b>	27400201
<b>eCl@ss 5.1</b>	27400201

# Ferrule - A 0,34- 7 - 3009202

## classifications

### eCl@ss

eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005


### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

## approvals

CSA / CSAus / cCSAus /

### Approval details

	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	

<b>CSAus</b>	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	

<b>cCSAus</b>
---------------

## Drawings