

## Insertion bridge - EB 80-12 - 3009338

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insertion bridge, Number of positions: 80, Color: gray

The figure shows a version of the article

### Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918091781

### Technical data

Technical data

<b>Color</b>	gray
<b>Material</b>	PA 6.6
<b>Number of positions</b>	80
<b>Inflammability class according to UL 94</b>	V2

### classifications

eCl@ss

<b>eCl@ss 4.0</b>	27141199
<b>eCl@ss 4.1</b>	27141199
<b>eCl@ss 5.0</b>	27141140
<b>eCl@ss 5.1</b>	27141140
<b>eCl@ss 6.0</b>	27141140
<b>eCl@ss 7.0</b>	27141140
<b>eCl@ss 8.0</b>	27141140

ETIM

<b>ETIM 2.0</b>	EC000489
<b>ETIM 3.0</b>	EC000489
<b>ETIM 4.0</b>	EC000489
<b>ETIM 5.0</b>	EC000489

UNSPSC

<b>UNSPSC 6.01</b>	30211829
<b>UNSPSC 7.0901</b>	39121426

## Insertion bridge - EB 80-12 - 3009338

### classifications

#### UNSPSC

<b>UNSPSC 11</b>	39121426
<b>UNSPSC 12.01</b>	39121426
<b>UNSPSC 13.2</b>	39121426

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>