

Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Lever-type fuse terminal block, black, for 6.3 x 32 mm G fuse inserts, with LED for 60 V DC

The illustration shows version ST 4-HESI (6,3X32)

Key commercial data

package_quantity	50
GTIN	4046356053549

Technical data

General

Number of levels	1
Number of connections	2
Color	black
Inflammability class according to UL 94	V0

General

Fuse	G / 6,3 x 32
Fuse type	Glass
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-3
Nominal current I_N	10 A
Nominal voltage U_N	60 V
Power loss	max. 2.5 W (With single arrangement of the fuse terminal block in the event of overload)
Power loss	max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of overload)
Power loss	max. 4 W (With single arrangement of the fuse terminal block in the event of a short-circuit)
Power loss	max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit)
Maximum current with single arrangement	10 A

Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

Technical data

General

LED voltage range	30 V AC/DC ... 60 V AC/DC
LED current range	0.4 mA ... 0.86 mA
Open side panel	nein

Dimensions

Width	8.2 mm
Length	76.5 mm
Height NS 35/7,5	68.9 mm
Height NS 35/15	76.4 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Connection method	Spring-cage connection
Minimum stripping length	8 mm
Maximum stripping length	10 mm
Internal cylindrical gage	A4

classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116

Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

classifications

eCl@ss

eCl@ss 8.0	27141116
------------	----------

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GL / RS / GOST /

Approval details

GL

RS

GOST 
--

accessories

Partition plate

ATP-QTC TWIN - 3206212



Screwdriver tools

Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

SZF 1-0,6X3,5 - 1204517



Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



Documentation

ST-IL - 3039900



Bridge

FBS 2-8 - 3030284



Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

FBS 3-8 - 3030297



FBS 4-8 - 3030307



FBS 5-8 - 3030310



FBS 10-8 - 3030323



RB ST 6-(2,5/4) - 3030860



Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

FBS 6-8 - 3032470



FBSRH 2-8 - 3033802



FBSRH 3-8 - 3033803



FBSRH 4-8 - 3033804



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Terminal marking

ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

UCT-TM 6 - 0828736



ZBF 8:UNBEDRUCKT - 0808781



UC-TMF 8 - 0818137



UCT-TMF 8 - 0828748



Labeled terminal marker

ZB 6 CUS - 0824992



Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

accessories

UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



ZBF 8 CUS - 0825030



UC-TMF 8 CUS - 0824654




UCT-TMF 8 CUS - 0829672



Drawings

Fuse modular terminal block - ST 4-HESILED 60 (6,3X32) - 3035182

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>