

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Coupling, Connection method: Spring-cage connection, Number of positions: 1, Cross section: 0.08 mm² - 4 mm², AWG: 28 - 12, Width: 5.2 mm, Height: 21.8 mm, Color: blue, Mounting type: On mounting plate

The illustration shows the version SC 2,5-RZ/1-L, in the design gray, blue and green-yellow

Product Features

- ✓ Using an engagement pin, these couplings can be plugged directly into the pre-drilled or punched mounting plate
- ✓ Types for self-assembly offer the option of direct mounting
- ✓ To ensure a secure fit, the bore holes must be burr-free

Key commercial data

package_quantity	50
GTIN	4017918922542

Technical data

General

Number of levels	1
Number of connections	1
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	24 A (with 2.5 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I _N	24 A
Nominal voltage U _N	500 V
Open side panel	ja
Number of positions	1

Dimensions

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

Technical data

Dimensions

Width	5.2 mm
Length	37.2 mm
Height	21.8 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm
Internal cylindrical gage	A3

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

classifications

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

approvals

UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / GOST / cULus Recognized /

Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm²/AWG/kcmil	26-12	26-12

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm²/AWG/kcmil	26-12	26-12

GOST 

LR

GL

BV

DNV

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

approvals



cULus Recognized 

accessories

End cover

D-SC 2,5 - 3042243



Mounting material

PDZ/2 - 3040562



PDZ/4 - 3040575



Labeled terminal marker

WST 2,5 - 3030941



Coupling - SC 2,5-RZ/ 1-L BU - 3042227

accessories

ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



Screwdriver tools

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

accessories

SZF 1-0,6X3,5 - 1204517



Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



Test plug terminal block

MPS-MT - 0201744



Insulating sleeve

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Coupling - SC 2,5-RZ/ 1-L BU - 3042227

accessories

MPS-IH BK - 0201731



ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



Drawings

Coupling - SC 2,5-RZ/ 1-L BU - 3042227

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>