

Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Fuse modular terminal block, Connection method: Screw connection, Cross section: 1.5 mm²- 25 mm², AWG: 18 - 3, Nominal current: 32 A, Nominal voltage: 1250 V, Width: 23 mm, Fuse type: gG / gPV / 10.3 x 85, Mounting type: NS 35/7,5, NS 35/15, Color: black

Key commercial data

package_quantity	5
GTIN	4046356657372

Technical data

General

Number of levels	1
Number of connections	2
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

General

Fuse	gG / gPV / 10.3 x 85
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	IIIa
Connection in acc. with standard	IEC 60269-1/-2
Nominal current I _N	32 A (the current and voltage are determined by the fuse)
Nominal voltage U _N	1250 V (the current and voltage are determined by the fuse)
Open side panel	nein
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	120 °C

Dimensions

Width	23 mm
Length	130 mm
Height NS 35/7,5	65.5 mm

Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

Technical data

Dimensions

Height NS 35/15	73 mm
-----------------	-------

Connection data

Conductor cross section solid min.	1.5 mm ²
Conductor cross section solid max.	25 mm ²
Conductor cross section stranded min.	0.75 mm ²
Conductor cross section stranded max.	25 mm ²
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	3
Conductor cross section stranded, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	16 mm ²
2 conductors with same cross section, solid min.	1.5 mm ²
2 conductors with same cross section, solid max.	4 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	10 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	4 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	10 mm ²
Connection method	Screw connection
Stripping length	11 mm
Internal cylindrical gage	A7
Screw thread	M5
Tightening torque, min	2.5 Nm
Tightening torque max	2.5 Nm

classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116

Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

classifications

eCl@ss

eCl@ss 8.0	27141116
------------	----------

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899


UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST /

Approval details



accessories

Screwdriver tools

SZS 1,0X4,0 VDE - 1205066



SF-SL 0,6X3,5-100 S-VDE - 1212587



Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

accessories

Fuse

FUSE 10,3X85 2A PV - 3062766



FUSE 10,3X85 4A PV - 3062767



FUSE 10,3X85 6A PV - 3062768



FUSE 10,3X85 8A PV - 3062769



FUSE 10,3X85 12A PV - 3062771



Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

accessories

FUSE 10,3X85 16A PV - 3062772



FUSE 10,3X85 20A PV - 3062773



Partition plate

TPN-UK - 3003062



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Fuse modular terminal block - UK 10,3-HESI 1500V - 3062760

accessories

End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Drawings

Circuit diagram

