

Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component terminal block, Connection method: Screw connection, Cross section: 0.14 mm² - 6 mm², AWG: 26 - 10, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Key commercial data

package_quantity	50
GTIN	4046356416252

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	8 kV
Surge voltage category	III
Nominal current I _N	0.5 A
Nominal voltage U _N	500 V
Open side panel	ja

Dimensions

Width	6.2 mm
Length	70.8 mm
Height NS 35/7,5	47.5 mm
Height NS 35/15	55 mm

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	6 mm ²

Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

Technical data

Connection data

Min. AWG conductor cross section, stranded	26
Max. AWG conductor cross section, stranded	10
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	0.14 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.14 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.14 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000903
ETIM 5.0	EC000903

Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

classifications

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121410
UNSPSC 13.2	39121411

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

Approval details

UL Recognized 				
Usegroups	B	C	D	
Nominal voltage UN	600 V	600 V		
Nominal current IN	0.5 A	0.5 A		
mm²/AWG/kcmil	26-10	26-10	26-10	

cUL Recognized 			
Usegroups	B	C	
Nominal voltage UN	300 V	300 V	300 V
Nominal current IN	0.5 A	0.5 A	0.5 A
mm²/AWG/kcmil	26-10	26-10	26-10

GOST 

cULus Recognized 

accessories

End cover

Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

D-UT 2,5/4-TWIN - 3047141



Test plug terminal block

PAI-4 - 3030925



PS-6 - 3030996



MPS-MT - 0201744



Screwdriver tools

SZS 0,6X3,5 - 1205053



Mounting rail

Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15-2,3 UNPERF 2000MM - 1201798



NS 35/15 AL UNPERF 2000MM - 1201756



Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 PERF 755MM - 1207640



NS 35/ 7,5 PERF 955MM - 1207653



NS 35/ 7,5 PERF 1155MM - 1207666



Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

NS 35/15 PERF 755MM - 1207679



NS 35/15 PERF 955MM - 1207682



NS 35/15 PERF 1155MM - 1207695



Terminal marking

ZB 6:UNBEDRUCKT - 1051003



Labeled terminal marker

ZB 6,LGS:FORTL.ZAHLEN - 1051016



Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

ZB 6,LGS:GLEICHE ZAHLEN - 1051032



ZB 6,QR:FORTL.ZAHLEN - 1051029



Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



Insulating sleeve

MPS-IH WH - 0201663



Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

MPS-IH RD - 0201676



MPS-IH GN - 0201702



MPS-IH BK - 0201731



End block

CLIPFIX 35-5 - 3022276



Bridge

FBS 2-6 - 3030336



Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

FBS 3-6 - 3030242



FBS 4-6 - 3030255



FBS 5-6 - 3030349



FBS 10-6 - 3030271



FBS 20-6 - 3030365



Component terminal block - UT 4-PE/L-DIO/L-R P/P - 3046834

accessories

ZB 6,QR:GLEICHE ZAHLEN - 1051045




ZB 6:SO/CMS - 1050499



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>