

Feed-through terminal block - UK 35 RD - 3048328

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Number of positions: 1, Cross section: 0.75 mm² - 50 mm², AWG: 18 - 1/0, Width: 15.1 mm, Color: red, Mounting type: NS 35/7,5, NS 35/15, NS 32

The illustration shows the version in gray

Product Features

- ✓ The large wiring space enables the connection of solid and stranded conductors without ferrules, even above the nominal cross section
- ✓ As well as saving space, the compact design enables user-friendly wiring in a small amount of space
- ✓ Optimum screwdriver guidance through closed screw shafts
- ✓ The multi-conductor connection offers maximum flexibility and wiring density



Key commercial data

package_quantity	50
GTIN	4017918954840

Technical data

General

Number of levels	1
Number of connections	2
Color	red
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	150 A (with 50 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	150 A
Nominal voltage U _N	1000 V

Feed-through terminal block - UK 35 RD - 3048328

Technical data

General

Open side panel	nein
Number of positions	1

Dimensions

Width	15.1 mm
Length	50 mm
Height NS 35/7,5	62 mm
Height NS 35/15	69.5 mm
Height NS 32	67 mm

Connection data

Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	50 mm ²
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	1/0
Conductor cross section stranded min.	0.75 mm ²
Conductor cross section stranded max.	35 mm ²
Min. AWG conductor cross section, stranded	18
Max. AWG conductor cross section, stranded	2
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	35 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	35 mm ²
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	16 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	10 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	10 mm ²
Connection method	Screw connection
Stripping length	16 mm
Internal cylindrical gage	B9
Screw thread	M6
Tightening torque, min	3.2 Nm
Tightening torque max	3.7 Nm

Feed-through terminal block - UK 35 RD - 3048328

Technical data

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / FM approved / UL Recognized / cUL Recognized / GL / cULus Recognized / CSA / UL Recognized / KEMA-KEUR / KEMA-KEUR / GOST / GL / RS / PRS / KR / NK / CCA / IECCEB Scheme / GOST /

Approval details

IECEX	
Nominal voltage UN	690 V
Nominal current IN	118.5 A
mm²/AWG/kcmil	0.75-35

ATEX 	
Nominal voltage UN	690 V
Nominal current IN	147 A

Feed-through terminal block - UK 35 RD - 3048328

approvals

mm²/AWG/kcmil	0.75-50

FM approved 	
Nominal voltage UN	600 V
Nominal current IN	150 A
mm²/AWG/kcmil	18

UL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	150 A
mm²/AWG/kcmil	

cUL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	150 A
mm²/AWG/kcmil	

GL 	
Nominal voltage UN	690 V
Nominal current IN	118.5 A
mm²/AWG/kcmil	35

cULus Recognized 	
---	--

CSA 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V

Feed-through terminal block - UK 35 RD - 3048328

approvals

Usegroups	B	C
Nominal current I _N	150 A	150 A
mm ² /AWG/kcmil	18	18

	
Nominal voltage U _N	600 V
Nominal current I _N	150 A
mm ² /AWG/kcmil	18

KEMA-KEUR 	
Nominal voltage U _N	1000 V
Nominal current I _N	
mm ² /AWG/kcmil	35

	
Nominal voltage U _N	1000 V
Nominal current I _N	
mm ² /AWG/kcmil	35

GOST 

--

RS

PRS

KR


NK

Feed-through terminal block - UK 35 RD - 3048328

approvals

CCA	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	35

IECEE CB Scheme 	
Nominal voltage UN	1000 V
Nominal current IN	
mm²/AWG/kcmil	35



accessories

Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



Terminal marking

Feed-through terminal block - UK 35 RD - 3048328

accessories

ZB 15:UNBEDRUCKT - 0811972



Labeled terminal marker

ZB 15 CUS - 0824945



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>