



INDICATOR LIGHT, 22MM, ROUND, METAL, SHINY, RED, SMOOTH LENS, WITH HOLDER, LED MODULE, WITH INTEGRATED LED 24V AC/DC, SCREW TERMINAL

Figure similar

| | |
|--|--|
| product brand name | SIRIUS ACT |
| Product designation | Commanding and signaling devices |
| Design of the product | Pilot Light |
| Manufacturer article number | |
| <ul style="list-style-type: none"> • of supplied LED module • of the supplied holder • of supplied repeater | 3SU1401-1BB20-1AA0 3SU1550-0AA10-0AA0 3SU1052-6AA20-0AA0 |

Actuator:

| | |
|--|----------|
| Product expansion optional Light source | Yes |
| Color | |
| <ul style="list-style-type: none"> • of the actuating element | Red |
| Material of the actuating element | plastic |
| Shape of the actuating element | round |
| Outer diameter of the actuating element | 29.45 mm |

Front ring:

| | |
|-------------------------------------|----|
| Product component front ring | No |
|-------------------------------------|----|

Holder:

| | |
|-------------------------------|-------|
| Material of the holder | Metal |
|-------------------------------|-------|

Display:

| | |
|------------------------------|---|
| Number of LED modules | 1 |
|------------------------------|---|

General technical data:

| | |
|--|-----|
| Product component | |
| <ul style="list-style-type: none"> • Light source | Yes |

| | |
|---|-----------------------------------|
| Insulation voltage | |
| • Rated value | 320 V |
| Type of voltage | |
| • of the operating voltage | AC/DC |
| Degree of pollution | 3 |
| Shock resistance | |
| • acc. to IEC 60068-2-27 | Sinusoidal half-wave 50 g / 11 ms |
| Vibration resistance | |
| • acc. to IEC 60068-2-6 | 10 ... 500 Hz: 5g |
| Surge voltage resistance Rated value | 4 kV |
| Protection class IP | IP66, IP67, IP69(IP69K) |
| • of the terminal | IP20 |
| Equipment marking | |
| • acc. to DIN EN 61346-2 | P |
| • acc. to DIN EN 81346-2 | P |
| Operating voltage | |
| • Rated value | 24 V |
| Relative positive tolerance of the operating voltage | 20 % |
| Relative negative tolerance of the operating voltage | 20 % |

Auxiliary circuit:

| | |
|------------------------------|---|
| Number of NC contacts | |
| • for auxiliary contacts | 0 |
| Number of NO contacts | |
| • for auxiliary contacts | 0 |
| Number of CO contacts | |
| • for auxiliary contacts | 0 |

Connections/ Terminals:

| | |
|--|------------------------------------|
| Type of electrical connection | |
| • of modules and accessories | Screw-type terminal |
| Type of connectable conductor cross-section | |
| • solid with core end processing | 2x (0.5 ... 0.75 mm ²) |
| • solid without core end processing | 2x (1.0 ... 1.5 mm ²) |
| • finely stranded with core end processing | 2x (0.5 ... 1.5 mm ²) |
| • finely stranded without core end processing | 2x (1,0 ... 1,5 mm ²) |
| • for AWG conductors | 2x (18 ... 14) |
| Tightening torque | |
| • with screw-type terminals | 0.8 ... 0.9 N·m |

Lamp:

| | |
|----------------------------------|-----|
| Type of light source | LED |
| Color of the light source | red |

Ambient conditions:

| | |
|--|----------------|
| Ambient temperature | |
| <ul style="list-style-type: none"> during operation | -25 ... +70 °C |
| <ul style="list-style-type: none"> during storage | -40 ... +80 °C |

Installation/ mounting/ dimensions:

| | |
|--|----------------------|
| Mounting type | front panel mounting |
| <ul style="list-style-type: none"> of modules and accessories | Front plate mounting |
| Height | 40 mm |
| Width | 30 mm |
| Shape of the installation opening | round |
| Mounting diameter | 22 mm |

Certificates/ approvals:

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU11526AA201AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3SU11526AA201AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU11526AA201AA0&lang=en



-P
24 V AC/DC



last modified:

27.04.2015