

Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Coupling, Connection method: Push-in connection, Number of positions: 3, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 14, Width: 10.5 mm, Height: 17.8 mm, Color: gray/blue/green-yellow

The figure shows the PPC 1,5/S/6 version

Product Features

- ✓ For secure and space-saving accommodation of plug-in contacts in cable ducts and distributor shafts
- ✓ The Push-in technology COMBI couplings for self-assembly provide solutions that users can implement themselves

Key commercial data

package_quantity	50
GTIN	4046356670906

Technical data

General

Number of connections	1
Color	gray/blue/green-yellow
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I _N	17.5 A
Nominal voltage U _N	500 V
Open side panel	ja
Number of positions	3

Dimensions

Width	10.5 mm
Length	27 mm
Height	17.8 mm

Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

Technical data

Connection data

Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	26
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1 mm ²
Connection method	Push-in connection
Stripping length	8 mm
Internal cylindrical gage	A1 / B1

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27141151
eCl@ss 7.0	27141151
eCl@ss 8.0	27141151

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002021
ETIM 5.0	EC002021

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121402
UNSPSC 12.01	39121402
UNSPSC 13.2	39121402

Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

accessories

End cover

D-PPC 1,5/S - 3213690



Screwdriver tools

SZF 0-0,4X2,5 - 1204504



Coding element

PC - 3040588



Cable housing

PH 1,5/S/3 - 3212756



PH 1,5/S/4 - 3212769



Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

accessories

PH 1,5/S/5 - 3212772



PH 1,5/S/6 - 3212785



PH 1,5/S/7 - 3212798



PH 1,5/S/8 - 3212808



PH 1,5/S/9 - 3212811



Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

accessories

PH 1,5/S/10 - 3212824



PH 1,5/S/11 - 3212837



PH 1,5/S/12 - 3212840



PH 1,5/S/13 - 3212853



PH 1,5/S/14 - 3212866



Terminal marking

Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

accessories

ZBF 3,5:UNBEDRUCKT - 0829392



UCT-TMF 3,5 - 0829486



Labeled terminal marker

ZBF 3,5 CUS - 0829394



UCT-TMF 3,5 CUS - 0829644



Test plug terminal block

MPS-MT - 0201744



Insulating sleeve

Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Coupling - PPC 1,5/S-NS/3 (1GY/1BU/1GNYE) - 3062126

accessories

MPS-IH BK - 0201731



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>