

## Disconnect terminal block - UT 4-PE/HEDI - 3074004

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Disconnect terminal block, Connection type: Screw connection, Cross section: 0.14 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 26 - 10, Nominal current: 20 A, Nominal voltage: 500 V, Length: 70.8 mm, Width: 6.2 mm, Color: Black/orange, Assembly: NS 35/7,5, NS 35/15

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 50            |
| GTIN             | 4046356416245 |

### Technical data

#### General

|                                         |              |
|-----------------------------------------|--------------|
| Number of levels                        | 1            |
| Number of connections                   | 2            |
| Color                                   | Black/orange |
| Insulating material                     | PA           |
| Inflammability class according to UL 94 | V0           |

#### General

|                                  |                                                       |
|----------------------------------|-------------------------------------------------------|
| Maximum load current             | 16 A (with 6 mm <sup>2</sup> conductor cross section) |
| Rated surge voltage              | 6 kV                                                  |
| Pollution degree                 | 3                                                     |
| Surge voltage category           | III                                                   |
| Insulating material group        | I                                                     |
| Connection in acc. with standard | IEC 60947-7-1 / IEC 60947-7-2                         |
| Nominal current I <sub>N</sub>   | 20 A                                                  |
| Nominal voltage U <sub>N</sub>   | 500 V                                                 |
| Open side panel                  | nein                                                  |

#### Dimensions

|                  |         |
|------------------|---------|
| Width            | 6.2 mm  |
| Length           | 70.8 mm |
| Height NS 35/7,5 | 73 mm   |
| Height NS 35/15  | 80.5 mm |

#### Connection data

|                                    |                      |
|------------------------------------|----------------------|
| Conductor cross section solid min. | 0.14 mm <sup>2</sup> |
| Conductor cross section solid max. | 6 mm <sup>2</sup>    |

# Disconnect terminal block - UT 4-PE/HEDI - 3074004

## Technical data

### Connection data

|                                                                                         |                      |
|-----------------------------------------------------------------------------------------|----------------------|
| Conductor cross section AWG/kcmil min.                                                  | 26                   |
| Conductor cross section AWG/kcmil max                                                   | 10                   |
| Conductor cross section stranded min.                                                   | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded max.                                                   | 6 mm <sup>2</sup>    |
| Min. AWG conductor cross section, stranded                                              | 26                   |
| Max. AWG conductor cross section, stranded                                              | 10                   |
| Conductor cross section stranded, with ferrule without plastic sleeve min.              | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max.              | 4 mm <sup>2</sup>    |
| Conductor cross section stranded, with ferrule with plastic sleeve min.                 | 0.14 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.                 | 4 mm <sup>2</sup>    |
| 2 conductors with same cross section, solid min.                                        | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, solid max.                                        | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded min.                                     | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded max.                                     | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min. | 0.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max. | 1.5 mm <sup>2</sup>  |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.   | 0.14 mm <sup>2</sup> |
| 2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.   | 1.5 mm <sup>2</sup>  |
| Connection method                                                                       | Screw connection     |
| Stripping length                                                                        | 9 mm                 |
| Internal cylindrical gage                                                               | A4                   |
| Screw thread                                                                            | M3                   |
| Tightening torque, min                                                                  | 0.6 Nm               |
| Tightening torque max                                                                   | 0.8 Nm               |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141118 |
| eCl@ss 4.1 | 27141118 |
| eCl@ss 5.0 | 27141118 |
| eCl@ss 5.1 | 27141118 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |
| eCl@ss 8.0 | 27141120 |

### ETIM

# Disconnect terminal block - UT 4-PE/HEDI - 3074004

## classifications

### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000901 |
| <b>ETIM 3.0</b> | EC000901 |
| <b>ETIM 4.0</b> | EC000901 |
| <b>ETIM 5.0</b> | EC000901 |

### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

## approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

### Approval details

| <b>UL Recognized</b>  |       |       |       |
|----------------------------------------------------------------------------------------------------------|-------|-------|-------|
| Usegroups                                                                                                | B     | C     |       |
| Nominal voltage UN                                                                                       | 600 V | 600 V | 600 V |
| Nominal current IN                                                                                       | 16 A  | 16 A  | 16 A  |
| mm <sup>2</sup> /AWG/kcmil                                                                               | 26-10 | 26-10 | 26-10 |

| <b>cUL Recognized</b>  |       |       |       |
|-----------------------------------------------------------------------------------------------------------|-------|-------|-------|
| Usegroups                                                                                                 | B     | C     |       |
| Nominal voltage UN                                                                                        | 600 V | 600 V | 600 V |
| Nominal current IN                                                                                        | 16 A  | 16 A  | 16 A  |
| mm <sup>2</sup> /AWG/kcmil                                                                                | 26-10 | 26-10 | 26-10 |

|                                                                                                 |  |  |  |
|-------------------------------------------------------------------------------------------------|--|--|--|
| <b>GOST</b>  |  |  |  |
|-------------------------------------------------------------------------------------------------|--|--|--|

|                                                                                                             |  |  |  |
|-------------------------------------------------------------------------------------------------------------|--|--|--|
| <b>cULus Recognized</b>  |  |  |  |
|-------------------------------------------------------------------------------------------------------------|--|--|--|

## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

#### Screwdriver tools

SZS 0,6X3,5 - 1205053



---

#### Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



---

#### Bridge

VS - 3004207



FBS 2-6 - 3030336



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

FBS 3-6 - 3030242



---

FBS 4-6 - 3030255



---

FBS 5-6 - 3030349



---

FBS 10-6 - 3030271



---

FBS 20-6 - 3030365



---

### Mounting rail

## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

---

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



---

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



---

NS 35/ 7,5 CAP - 1206560



---

NS 35/15 PERF 2000MM - 1201730



---

NS 35/15 UNPERF 2000MM - 1201714



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

NS 35/15 WH PERF 2000MM - 0806602



---

NS 35/15 WH UNPERF 2000MM - 1204135



---

NS 35/15 AL UNPERF 2000MM - 1201756



---

NS 35/15 ZN PERF 2000MM - 1206599



---

NS 35/15 ZN UNPERF 2000MM - 1206586



---

NS 35/15 CU UNPERF 2000MM - 1201895





## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

---

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



---

### Terminal marking

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

ZB 6:UNBEDRUCKT - 1051003



---

UC-TM 6 - 0818085



---

UCT-TM 6 - 0828736



---

### Labeled terminal marker

ZB 5 CUS - 0824962



---

UC-TM 5 CUS - 0824581



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

UCT-TM 5 CUS - 0829595



ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



### End block

CLIPFIX 35 - 3022218



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



### Test plug terminal block

PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



## Disconnect terminal block - UT 4-PE/HEDI - 3074004

### accessories

PAI-4-FIX-5/6 RD - 3035976



---

PAI-4-FIX-5/6 GN - 3035978



---

PAI-4-FIX-5/6 BK - 3035980



---

PAI-4-FIX-5/6 GY - 3035982



---

PAI-4-FIX-5/6 VT - 3035979



---

PAI-4-FIX-5/6 BN - 3035981




## Disconnect terminal block - UT 4-PE/HEDI - 3074004

accessories

---

### Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>