

Fuse modular terminal block - UK-SILED 24 BK - 3118520

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Fuse modular terminal block, Connection method: Screw connection, Cross section: 0.2 mm²- 4 mm², AWG: 24 - 12, Nominal current: 6.3 A, Nominal voltage: 250 V, Width: 8.2 mm, Fuse type: G / 5 x 20 / 5 x 25, Mounting type: NS 32, NS 35/7,5, NS 35/15, Color: black

The figure shows a version of the article

Key commercial data

package_quantity	50
GTIN	4017918283322

Technical data

General

Number of levels	1
Number of connections	2
Color	black
Inflammability class according to UL 94	V0

General

Fuse	G / 5 x 20 / 5 x 25
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I _N	6.3 A
Nominal voltage U _N	250 V (As a fuse terminal block)
Nominal voltage U _N	400 V (As a disconnect terminal block)
Open side panel	nein

Dimensions

Width	8.2 mm
Length	59.5 mm
Height NS 35/7,5	58.4 mm
Height NS 35/15	65.9 mm
Height NS 32	63.3 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
------------------------------------	---------------------

Fuse modular terminal block - UK-SILED 24 BK - 3118520

Technical data

Connection data

Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
Connection method	Screw connection
Stripping length	9 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

Fuse modular terminal block - UK-SILED 24 BK - 3118520

classifications



UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

approvals

GOST / GOST /

Approval details



accessories

Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



Drawings