

Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator terminal block, Connection method: Spring-cage connection, Cross section: 0.08 mm² - 4 mm², AWG: 28 - 12, Width: 5.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ✓ Three-conductor output terminal block of the same shape with PE connection in the lower level for wiring actuators
- ✓ Power terminal blocks can be located at any point on the terminal strip for supply or extension purposes
- ✓ Versions with LED for indicating the switching states
- ✓ Easy bridging and potential distribution using the patented plug-in bridges from the CLIPLINE complete system
- ✓ For space and time-saving wiring of three-conductor initiators and actuators
- ✓ Potential is supplied via the STIO-IN power terminal blocks
- ✓ The upper level is for signal wiring, whereas the two lower levels are used to distribute the positive and negative potential

Key commercial data

package_quantity	50
GTIN	4046356143530

Technical data

General

Number of levels	3
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	18 A
Nominal voltage U _N	24 V (Light indicator, red)
Open side panel	ja

Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

Technical data

Dimensions

Width	5.2 mm
Length	75 mm
Height NS 35/7,5	44.5 mm
Height NS 35/15	52 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141128
eCl@ss 7.0	27141128
eCl@ss 8.0	27141128

ETIM

ETIM 2.0	EC000900
ETIM 3.0	EC000900
ETIM 4.0	EC000900
ETIM 5.0	EC000900

UNSPSC

UNSPSC 6.01	30211811
-------------	----------

Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

classifications

UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	10 A	18 A	10 A
mm²/AWG/kcmil	28-12	28-12	28-12

cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	10 A	18 A	10 A
mm²/AWG/kcmil	28-12	28-12	28-12

cULus Recognized 			
---	--	--	--

accessories

End cover

D-STIO 2,5/3 - 3209112



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

Documentation

ST-IL - 3039900



Bridge

FBS 2-5 - 3030161



FBS 3-5 - 3030174



FBS 4-5 - 3030187



FBS 5-5 - 3030190



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

FBS 10-5 - 3030213



FBS 20-5 - 3030226



FBS 50-5 - 3038930



FBS 2-5 BU - 3036877



FBS 3-5 BU - 3036880



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

FBS 4-5 BU - 3036893



FBS 5-5 BU - 3036903



FBS 10-5 BU - 3036916



FBS 20-5 BU - 3036929



FBS 50-5 BU - 3032114



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

FBS 2-5 GY - 3038969



FBS 3-5 GY - 3038972



FBS 4-5 GY - 3038985



FBS 5-5 GY - 3038998



FBS 10-5 GY - 3039007



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

FBS 20-5 GY - 3038671



FBS 50-5 GY - 3032127



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

NS 35/ 7,5 CAP - 1206560



Terminal marking

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



ZBF 5:UNBEDRUCKT - 0808642



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



Labeled terminal marker

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



Sensor/actuator terminal block - STIO 2,5/3-2B/L-LA24RD/O-M - 3209028

accessories

ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>