

# Fuse modular terminal block - USIG MIT ST-SI - 5022106

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Fuse modular terminal block, with fuse plug, Connection method: Screw connection, Cross section: 0.5 mm<sup>2</sup>- 16 mm<sup>2</sup>, AWG: 20 - 6, Nominal current: 10 A, Nominal voltage: 500 V, Width: 10.2 mm, Fuse type: G / 5 x 20 / 5 x 25 / 5 x 30 / 6.3 x 32, Fuse type: Glass, Mounting type: NS 35/7,5, NS 35/15, NS 32, Color: black

## Key commercial data

package_quantity	50
GTIN	4017918285821

## Technical data

### General

Number of levels	1
Number of connections	2
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

### General

Fuse	G / 5 x 20 / 5 x 25 / 5 x 30 / 6.3 x 32
Fuse type	Glass
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-3
Nominal current I <sub>N</sub>	10 A
Nominal voltage U <sub>N</sub>	500 V (As a fuse terminal block)
Nominal voltage U <sub>N</sub>	500 V (As a disconnect terminal block)
Open side panel	nein

### Dimensions

Width	10.2 mm
Length	61 mm
Height NS 35/7,5	51.6 mm
Height NS 35/15	59.1 mm
Height NS 32	59.1 mm

# Fuse modular terminal block - USIG MIT ST-SI - 5022106

## Technical data

### Connection data

Conductor cross section solid min.	0.5 mm <sup>2</sup>
Conductor cross section solid max.	16 mm <sup>2</sup>
Conductor cross section stranded min.	0.5 mm <sup>2</sup>
Conductor cross section stranded max.	16 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm <sup>2</sup>
2 conductors with same cross section, solid min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, solid max.	4 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	6 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	6 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm <sup>2</sup>
Cross section with insertion bridge, solid max.	16 mm <sup>2</sup>
Cross section with insertion bridge, stranded max.	16 mm <sup>2</sup>
Connection method	Screw connection
Stripping length	13 mm
Internal cylindrical gage	A5
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

## classifications

### eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116

# Fuse modular terminal block - USIG MIT ST-SI - 5022106

## classifications

eCl@ss

eCl@ss 8.0	27141116
------------	----------

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899


UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## approvals

GOST / GOST /

### Approval details



## accessories

### Partition plate

ATS-GSK - 0304227



## Terminal marking

# Fuse modular terminal block - USIG MIT ST-SI - 5022106

## accessories

SBS10:UNBEDRUCKT - 1007248



ZB 10:UNBEDRUCKT - 1053001



UC-TM 10 - 0818069



UCT-TM 10 - 0829142



## Bridge

EB 2-10 - 0203153



# Fuse modular terminal block - USIG MIT ST-SI - 5022106

accessories

EB 10-10 - 0203137



---

## Fuse

ST 1-SI - 0920326



---

ST 1-SILED 24 - 0920384



---

ST 1-SILA 250 - 0920397



---

## Plug

ST-T - 0920216



---

## Mounting rail

## Fuse modular terminal block - USIG MIT ST-SI - 5022106

### accessories

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



## Fuse modular terminal block - USIG MIT ST-SI - 5022106

accessories

---

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



## Fuse modular terminal block - USIG MIT ST-SI - 5022106

### accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599





## Fuse modular terminal block - USIG MIT ST-SI - 5022106

accessories

---

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



---

### Labeled terminal marker

ZB 10 CUS - 0824941



## Fuse modular terminal block - USIG MIT ST-SI - 5022106

### accessories

UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



### End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



# Fuse modular terminal block - USIG MIT ST-SI - 5022106

accessories

E/UK - 1201442




E/UK 1 - 1201413




## Drawings

Circuit diagram



# Fuse modular terminal block - USIG MIT ST-SI - 5022106

Circuit diagram



1 = partition plate  
2 = insertion bridge

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>