

# Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Highly flexible textile label, continuous, cassette, white with black imprint, mounting type: adhesive, can be marked with THERMOFOX

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4055626212159

## Technical data

### Dimensions

<b>Length (b)</b>	6 m
<b>Width (a)</b>	18 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	0 °C ... 80 °C
<b>Recommended storage conditions</b>	5 - 35°C / 30 - 80 % relative humidity. Storage in a cool and dry place in the original packaging is recommended.

### General

<b>Color</b>	white
<b>Components</b>	free from silicone, halogen, and cadmium
<b>Material</b>	PA
<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>RoHS compliant</b>	Yes
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02
<b>Result</b>	Test passed
<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h
<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN 60068-2-11:2000-02
<b>Test duration</b>	96 h
<b>Salt spray testing result</b>	Test passed
<b>Wipe resistance of test specification inscriptions</b>	DIN EN 61010-1 (VDE 0411-1):2011-07
<b>Result</b>	Test passed
<b>Marking mounting type</b>	Adhesive

## Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936

### Technical data

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27149129
eCl@ss 9.0	27400629

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288
ETIM 6.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

### Drawings

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>