




Data sheet | Item number: 2003-6651

Multilevel installation terminal block; 4 mm<sup>2</sup>; N; Push-in CAGE CLAMP®



[www.wago.com/2003-6651](http://www.wago.com/2003-6651)



Data

Electrical data

Ratings per IEC/EN 60664-1

|                                 |   |
|---------------------------------|---|
| Rated voltage (III / 3)         | 400 V   |
| Rated impulse voltage (III / 3) | 6 kV  |
| Rated current                   | 25 A  |
| Legend (ratings)                | (III / 3) ≙ Overvoltage category III / Pollution degree 3 |

### Approvals per UL 1059

|                                |       |
|--------------------------------|-------|
| Rated voltage UL (Use Group B) | 300 V |
| Rated current UL (Use Group B) | 20 A  |
| Rated voltage UL (Use Group C) | 300 V |
| Rated current UL (Use Group C) | 20 A  |

### Approvals per CSA

|                                 |       |
|---------------------------------|-------|
| Rated voltage CSA (Use Group C) | 300 V |
| Rated current CSA (Use Group C) | 20 A  |

### Connection data

|   |  |
|---|--|
| Connection technology   | Push-in CAGE CLAMP®                        |
| Actuation type  | Push-in<br>Operating tool                  |
| Connectable conductor materials                                 | Copper                                     |
| Nominal cross section   | 2.5 mm <sup>2</sup>                        |
| Solid conductor   | 0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG |
| Solid conductor, push-in termination                            | 0.75 ... 4 mm <sup>2</sup> / 18 ... 12 AWG |
| Fine-stranded conductor   | 0.25 ... 4 mm <sup>2</sup> / 22 ... 12 AWG |
| Fine-stranded conductor with ferrule, push-in termination, from | 0.75 mm <sup>2</sup> / 18 AWG              |
| Strip length  | 10 ... 12 mm / 0.39 ... 0.47 Inch          |
| Total number of connection points                               | 2  |
| Total number of potentials                                      | 1  |
| Number of levels  | 1  |
| Type of wiring  | Front-entry wiring                         |

### Geometrical Data

|                                       |                      |
|---------------------------------------|----------------------|
| Width                                 | 5.2 mm / 0.205 inch  |
| Height from upper-edge of DIN-35 rail | 44.3 mm / 1.744 inch |
| Depth                                 | 110 mm / 4.331 inch  |

### Mechanical data

|                   |                     |
|-------------------|---------------------|
| Design            | angled              |
| Type of mounting  | DIN-35 rail         |
| Potential marking | N                   |
| Marking level     | Center/side marking |

## Material Data




|                     |                      |
|---------------------|----------------------|
| Color               | gray                 |
| Insulating material | Polyamide 66 (PA 66) |
| Fire load           | 0.306 MJ             |
| Weight              | 12.686 g             |

## Commercial data

|                    |               |
|--------------------|---------------|
| Country of origin  | CN            |
| GTIN               | 4050821322092 |
| Customs Tariff No. | 85369010000   |
| Product Group      | 22 (TOPJOB S) |

## Approvals / Certificates

### Country specific Approvals

| Logo   | Approval                        | Certificate name |
|--|---------------------------------|------------------|
|   | CCA<br>DEKRA Certification B.V. | 2196143:01       |
|  | CCA<br>DEKRA Certification B.V. | NTR NL 7519      |
|  | CSA<br>DEKRA Certification B.V. | 70111102         |

### UL-Approvals

















| Logo   | Approval                             | Certificate name |
|--|--------------------------------------|------------------|
|  | UL<br>Underwriters Laboratories Inc. | E45172           |

## Compatible products

### End plate

|  |   |  |
|--|---|--|
|  | Item no.: 2003-6692<br>End and intermediate plate; 0.8 mm thick | <a href="http://www.wago.com/2003-6692">www.wago.com/2003-6692</a> |
|--|---|--|

### Jumper

|  |   |  |
|--|---|--|
|    | <b>Item no.: 2002-400</b><br>Adjacent jumper for continuous commoning; insulated; 2-way; Nominal current 25 A | <a href="http://www.wago.com/2002-400">www.wago.com/2002-400</a>                 |
|    | <b>Item no.: 2002-402</b><br>Push-in type jumper bar; insulated; 2-way; Nominal current 25 A                  | <a href="http://www.wago.com/2002-402">www.wago.com/2002-402</a>                 |
|    | <b>Item no.: 2002-402/000-005</b><br>Push-in type jumper bar; insulated; 2-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-402/000-005">www.wago.com/2002-402/000-005</a> |
|    | <b>Item no.: 2002-402/000-006</b><br>Push-in type jumper bar; insulated; 2-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-402/000-006">www.wago.com/2002-402/000-006</a> |
|    | <b>Item no.: 2002-403</b><br>Push-in type jumper bar; insulated; 3-way; Nominal current 25 A                  | <a href="http://www.wago.com/2002-403">www.wago.com/2002-403</a>                 |
|    | <b>Item no.: 2002-403/000-005</b><br>Push-in type jumper bar; insulated; 3-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-403/000-005">www.wago.com/2002-403/000-005</a> |
|    | <b>Item no.: 2002-403/000-006</b><br>Push-in type jumper bar; insulated; 3-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-403/000-006">www.wago.com/2002-403/000-006</a> |
|    | <b>Item no.: 2002-404</b><br>Push-in type jumper bar; insulated; 4-way; Nominal current 25 A                  | <a href="http://www.wago.com/2002-404">www.wago.com/2002-404</a>                 |
|  | <b>Item no.: 2002-404/000-005</b><br>Push-in type jumper bar; insulated; 4-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-404/000-005">www.wago.com/2002-404/000-005</a> |
|  | <b>Item no.: 2002-404/000-006</b><br>Push-in type jumper bar; insulated; 4-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-404/000-006">www.wago.com/2002-404/000-006</a> |
|  | <b>Item no.: 2002-405</b><br>Push-in type jumper bar; insulated; 5-way; Nominal current 25 A                  | <a href="http://www.wago.com/2002-405">www.wago.com/2002-405</a>                 |
|  | <b>Item no.: 2002-405/000-005</b><br>Push-in type jumper bar; insulated; 5-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-405/000-005">www.wago.com/2002-405/000-005</a> |
|  | <b>Item no.: 2002-405/000-006</b><br>Push-in type jumper bar; insulated; 5-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-405/000-006">www.wago.com/2002-405/000-006</a> |
|  | <b>Item no.: 2002-405/011-000</b><br>Star point jumper; insulated; 3-way (1-3-5); IN = IN terminal block      | <a href="http://www.wago.com/2002-405/011-000">www.wago.com/2002-405/011-000</a> |
|  | <b>Item no.: 2002-406</b><br>Push-in type jumper bar; insulated; 6-way; Nominal current 25 A                  | <a href="http://www.wago.com/2002-406">www.wago.com/2002-406</a>                 |
|  | <b>Item no.: 2002-406/000-005</b><br>Push-in type jumper bar; insulated; 6-way; Nominal current 25 A          | <a href="http://www.wago.com/2002-406/000-005">www.wago.com/2002-406/000-005</a> |



**Item no.: 2002-406/000-006**  
Push-in type jumper bar; insulated; 6-way; Nominal current 25 A

[www.wago.com/2002-406/000-006](http://www.wago.com/2002-406/000-006)



**Item no.: 2002-406/020-000**  
Delta jumper; insulated; 1-2 3-4 5-6; IN = IN terminal block

[www.wago.com/2002-406/020-000](http://www.wago.com/2002-406/020-000)



**Item no.: 2002-407**  
Push-in type jumper bar; insulated; 7-way; Nominal current 25 A

[www.wago.com/2002-407](http://www.wago.com/2002-407)



**Item no.: 2002-407/000-005**  
Push-in type jumper bar; insulated; 7-way; Nominal current 25 A

[www.wago.com/2002-407/000-005](http://www.wago.com/2002-407/000-005)



**Item no.: 2002-407/000-006**  
Push-in type jumper bar; insulated; 7-way; Nominal current 25 A

[www.wago.com/2002-407/000-006](http://www.wago.com/2002-407/000-006)



**Item no.: 2002-408**  
Push-in type jumper bar; insulated; 8-way; Nominal current 25 A

[www.wago.com/2002-408](http://www.wago.com/2002-408)



**Item no.: 2002-408/000-005**  
Push-in type jumper bar; insulated; 8-way; Nominal current 25 A

[www.wago.com/2002-408/000-005](http://www.wago.com/2002-408/000-005)



**Item no.: 2002-408/000-006**  
Push-in type jumper bar; insulated; 8-way; Nominal current 25 A

[www.wago.com/2002-408/000-006](http://www.wago.com/2002-408/000-006)



**Item no.: 2002-409**  
Push-in type jumper bar; insulated; 9-way; Nominal current 25 A

[www.wago.com/2002-409](http://www.wago.com/2002-409)



**Item no.: 2002-409/000-005**  
Push-in type jumper bar; insulated; 9-way; Nominal current 25 A

[www.wago.com/2002-409/000-005](http://www.wago.com/2002-409/000-005)



**Item no.: 2002-409/000-006**  
Push-in type jumper bar; insulated; 9-way; Nominal current 25 A

[www.wago.com/2002-409/000-006](http://www.wago.com/2002-409/000-006)



**Item no.: 2002-410**  
Push-in type jumper bar; insulated; 10-way; Nominal current 25 A

[www.wago.com/2002-410](http://www.wago.com/2002-410)



**Item no.: 2002-410/000-005**  
Push-in type jumper bar; insulated; 10-way; Nominal current 25 A

[www.wago.com/2002-410/000-005](http://www.wago.com/2002-410/000-005)



**Item no.: 2002-410/000-006**  
Push-in type jumper bar; insulated; 10-way; Nominal current 25 A

[www.wago.com/2002-410/000-006](http://www.wago.com/2002-410/000-006)

















**Item no.: 2002-423**  
Push-in type jumper bar; insulated; from 1 to 3; Nominal current 25 A











[www.wago.com/2002-423](http://www.wago.com/2002-423)







**Item no.: 2002-423/000-005**  
Adjacent jumper for continuous commoning; insulated; from 1 to 3; Nominal current 25 A

















[www.wago.com/2002-423/000-005](http://www.wago.com/2002-423/000-005)

|  |   |  |
|--|---|--|
|    | <b>Item no.: 2002-423/000-006</b><br>Adjacent jumper for continuous commoning; insulated; from 1 to 3; Nominal current 25 A   | <a href="http://www.wago.com/2002-423/000-006">www.wago.com/2002-423/000-006</a> |
|    | <b>Item no.: 2002-433</b><br>Push-in type jumper bar; insulated; from 1 to 3; Nominal current 25 A  | <a href="http://www.wago.com/2002-433">www.wago.com/2002-433</a>                 |
|    | <b>Item no.: 2002-434</b><br>Push-in type jumper bar; insulated; from 1 to 4; Nominal current 25 A  | <a href="http://www.wago.com/2002-434">www.wago.com/2002-434</a>                 |
|    | <b>Item no.: 2002-435</b><br>Push-in type jumper bar; insulated; from 1 to 5; Nominal current 25 A  | <a href="http://www.wago.com/2002-435">www.wago.com/2002-435</a>                 |
|    | <b>Item no.: 2002-436</b><br>Push-in type jumper bar; insulated; from 1 to 6; Nominal current 25 A  | <a href="http://www.wago.com/2002-436">www.wago.com/2002-436</a>                 |
|    | <b>Item no.: 2002-437</b><br>Push-in type jumper bar; insulated; from 1 to 7; Nominal current 25 A  | <a href="http://www.wago.com/2002-437">www.wago.com/2002-437</a>                 |
|    | <b>Item no.: 2002-438</b><br>Push-in type jumper bar; insulated; from 1 to 8; Nominal current 25 A  | <a href="http://www.wago.com/2002-438">www.wago.com/2002-438</a>                 |
|    | <b>Item no.: 2002-439</b><br>Push-in type jumper bar; insulated; from 1 to 9; Nominal current 25 A  | <a href="http://www.wago.com/2002-439">www.wago.com/2002-439</a>                 |
|   | <b>Item no.: 2002-440</b><br>Push-in type jumper bar; insulated; from 1 to 10; Nominal current 25 A   | <a href="http://www.wago.com/2002-440">www.wago.com/2002-440</a>                 |
|  | <b>Item no.: 2002-472</b><br>Staggered jumper; insulated; 2-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks                             | <a href="http://www.wago.com/2002-472">www.wago.com/2002-472</a>                 |
|  | <b>Item no.: 2002-473</b><br>Staggered jumper; insulated; 3-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks                             | <a href="http://www.wago.com/2002-473">www.wago.com/2002-473</a>                 |
|  | <b>Item no.: 2002-473/011-000</b><br>Ready-made staggered jumper; insulated; 2-way (1-3); Nominal current 25 A; with contact lugs broken off at the factory and circuit marking   | <a href="http://www.wago.com/2002-473/011-000">www.wago.com/2002-473/011-000</a> |
|  | <b>Item no.: 2002-474</b><br>Staggered jumper; insulated; 4-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks                             | <a href="http://www.wago.com/2002-474">www.wago.com/2002-474</a>                 |
|  | <b>Item no.: 2002-475</b><br>Staggered jumper; insulated; 5-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks                             | <a href="http://www.wago.com/2002-475">www.wago.com/2002-475</a>                 |
|  | <b>Item no.: 2002-475/011-000</b><br>Ready-made staggered jumper; insulated; 3-way (1-3-5); Nominal current 25 A; with contact lugs broken off at the factory and circuit marking | <a href="http://www.wago.com/2002-475/011-000">www.wago.com/2002-475/011-000</a> |
|  | <b>Item no.: 2002-476</b><br>Staggered jumper; insulated; 6-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks                             | <a href="http://www.wago.com/2002-476">www.wago.com/2002-476</a>                 |
|  | <b>Item no.: 2002-477</b><br>Staggered jumper; insulated; 7-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks                             | <a href="http://www.wago.com/2002-477">www.wago.com/2002-477</a>                 |
|  | <b>Item no.: 2002-477/011-000</b><br>Ready-made staggered jumper; insulated; 1-3-5-7; Nominal current 25 A; with contact lugs broken off at the factory and circuit marking       | <a href="http://www.wago.com/2002-477/011-000">www.wago.com/2002-477/011-000</a> |

|  |  |  |
|--|--|--|
|    | <b>Item no.: 2002-478</b><br>Staggered jumper; insulated; 8-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks  | <a href="http://www.wago.com/2002-478">www.wago.com/2002-478</a>                 |
|    | <b>Item no.: 2002-479</b><br>Staggered jumper; insulated; 9-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks  | <a href="http://www.wago.com/2002-479">www.wago.com/2002-479</a>                 |
|  | <b>Item no.: 2002-479/011-000</b><br>Ready-made staggered jumper; insulated; 1-3-5-7-9; Nominal current 25 A; with contact lugs broken off at the factory and circuit marking                                  | <a href="http://www.wago.com/2002-479/011-000">www.wago.com/2002-479/011-000</a> |
|    | <b>Item no.: 2002-480</b><br>Staggered jumper; insulated; 10-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks   | <a href="http://www.wago.com/2002-480">www.wago.com/2002-480</a>                 |
|    | <b>Item no.: 2002-481</b><br>Staggered jumper; insulated; 11-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks   | <a href="http://www.wago.com/2002-481">www.wago.com/2002-481</a>                 |
|  | <b>Item no.: 2002-481/011-000</b><br>Ready-made staggered jumper; insulated; 1-3-5-7-9-11; Nominal current 25 A; with contact lugs broken off at the factory and circuit marking                               | <a href="http://www.wago.com/2002-481/011-000">www.wago.com/2002-481/011-000</a> |
|    | <b>Item no.: 2002-482</b><br>Staggered jumper; insulated; 12-way; Nominal current 25 A; suitable for 2002 and 2003 Series rail-mounted terminal blocks   | <a href="http://www.wago.com/2002-482">www.wago.com/2002-482</a>                 |
|   | <b>Item no.: 2009-412</b><br>Push-in type wire jumper; insulated; wire length 60 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks  | <a href="http://www.wago.com/2009-412">www.wago.com/2009-412</a>                 |
|  | <b>Item no.: 2009-414</b><br>Push-in type wire jumper; insulated; wire length 110 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks | <a href="http://www.wago.com/2009-414">www.wago.com/2009-414</a>                 |
|  | <b>Item no.: 2009-416</b><br>Push-in type wire jumper; insulated; wire length 250 mm; Conductor cross section 1.5 mm <sup>2</sup> ; suitable for 2001, 2002, 2003 and 2022 Series rail-mounted terminal blocks | <a href="http://www.wago.com/2009-416">www.wago.com/2009-416</a>                 |
|  | <b>Item no.: 210-103</b><br>Wire commoning chain; insulated; 50 connections  | <a href="http://www.wago.com/210-103">www.wago.com/210-103</a>                   |
|  | <b>Item no.: 210-123</b><br>Wire commoning chain; insulated; 50 connections  | <a href="http://www.wago.com/210-123">www.wago.com/210-123</a>                   |

#### Marking accessories

|  |   |  |
|--|---|--|
|  | <b>Item no.: 2009-110</b><br>Marking strips; on reel; not stretchable; plain; snap-on type                              | <a href="http://www.wago.com/2009-110">www.wago.com/2009-110</a>                 |
|  | <b>Item no.: 2009-115</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type         | <a href="http://www.wago.com/2009-115">www.wago.com/2009-115</a>                 |
|  | <b>Item no.: 2009-115/000-002</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-002">www.wago.com/2009-115/000-002</a> |
|  | <b>Item no.: 2009-115/000-006</b><br>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type | <a href="http://www.wago.com/2009-115/000-006">www.wago.com/2009-115/000-006</a> |

|  |  |  |
|--|--|--|
|   | <p><b>Item no.: 2009-115/000-007</b><br/>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>      | <a href="http://www.wago.com/2009-115/000-007">www.wago.com/2009-115/000-007</a> |
|   | <p><b>Item no.: 2009-115/000-012</b><br/>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>      | <a href="http://www.wago.com/2009-115/000-012">www.wago.com/2009-115/000-012</a> |
|   | <p><b>Item no.: 2009-115/000-017</b><br/>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>      | <a href="http://www.wago.com/2009-115/000-017">www.wago.com/2009-115/000-017</a> |
|   | <p><b>Item no.: 2009-115/000-023</b><br/>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>      | <a href="http://www.wago.com/2009-115/000-023">www.wago.com/2009-115/000-023</a> |
|   | <p><b>Item no.: 2009-115/000-024</b><br/>WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>      | <a href="http://www.wago.com/2009-115/000-024">www.wago.com/2009-115/000-024</a> |
|    | <p><b>Item no.: 2009-145</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>         | <a href="http://www.wago.com/2009-145">www.wago.com/2009-145</a>                 |
|    | <p><b>Item no.: 2009-145/000-002</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p> | <a href="http://www.wago.com/2009-145/000-002">www.wago.com/2009-145/000-002</a> |
|   | <p><b>Item no.: 2009-145/000-005</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p> | <a href="http://www.wago.com/2009-145/000-005">www.wago.com/2009-145/000-005</a> |
|  | <p><b>Item no.: 2009-145/000-006</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p> | <a href="http://www.wago.com/2009-145/000-006">www.wago.com/2009-145/000-006</a> |
|  | <p><b>Item no.: 2009-145/000-007</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p> | <a href="http://www.wago.com/2009-145/000-007">www.wago.com/2009-145/000-007</a> |
|  | <p><b>Item no.: 2009-145/000-012</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p> | <a href="http://www.wago.com/2009-145/000-012">www.wago.com/2009-145/000-012</a> |
|  | <p><b>Item no.: 2009-145/000-023</b><br/>Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p> | <a href="http://www.wago.com/2009-145/000-023">www.wago.com/2009-145/000-023</a> |
|  | <p><b>Item no.: 2009-145/000-024</b><br/>Mini-WSB Inline; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>                   | <a href="http://www.wago.com/2009-145/000-024">www.wago.com/2009-145/000-024</a> |
|  | <p><b>Item no.: 2009-191</b><br/>Group marker carrier</p>  | <a href="http://www.wago.com/2009-191">www.wago.com/2009-191</a>                 |
|  | <p><b>Item no.: 2009-192</b><br/>Group marker carrier</p>  | <a href="http://www.wago.com/2009-192">www.wago.com/2009-192</a>                 |
|  | <p><b>Item no.: 2009-193</b><br/>Group marker carrier</p>  | <a href="http://www.wago.com/2009-193">www.wago.com/2009-193</a>                 |





**Item no.: 2009-198**  
Adaptor

[www.wago.com/2009-198](http://www.wago.com/2009-198)



**Item no.: 248-501**  
Miniature WSB Quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card

[www.wago.com/248-501](http://www.wago.com/248-501)



**Item no.: 248-501/000-002**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-002](http://www.wago.com/248-501/000-002)



**Item no.: 248-501/000-005**  
Mini-WSB marking card; as card; plain; snap-on type

[www.wago.com/248-501/000-005](http://www.wago.com/248-501/000-005)



**Item no.: 248-501/000-006**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-006](http://www.wago.com/248-501/000-006)



**Item no.: 248-501/000-007**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-007](http://www.wago.com/248-501/000-007)



**Item no.: 248-501/000-012**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-012](http://www.wago.com/248-501/000-012)



**Item no.: 248-501/000-017**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-017](http://www.wago.com/248-501/000-017)



**Item no.: 248-501/000-023**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-023](http://www.wago.com/248-501/000-023)



**Item no.: 248-501/000-024**  
Mini-WSB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/248-501/000-024](http://www.wago.com/248-501/000-024)



**Item no.: 793-501**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501](http://www.wago.com/793-501)



**Item no.: 793-501/000-002**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-002](http://www.wago.com/793-501/000-002)



**Item no.: 793-501/000-005**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-005](http://www.wago.com/793-501/000-005)



**Item no.: 793-501/000-006**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-006](http://www.wago.com/793-501/000-006)



**Item no.: 793-501/000-007**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-007](http://www.wago.com/793-501/000-007)



**Item no.: 793-501/000-012**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-012](http://www.wago.com/793-501/000-012)



**Item no.: 793-501/000-017**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-017](http://www.wago.com/793-501/000-017)



**Item no.: 793-501/000-023**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-023](http://www.wago.com/793-501/000-023)



**Item no.: 793-501/000-024**  
WMB marking card; as card; not stretchable; plain; snap-on type

[www.wago.com/793-501/000-024](http://www.wago.com/793-501/000-024)



**Item no.: 793-5501**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501](http://www.wago.com/793-5501)



**Item no.: 793-5501/000-002**  
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-002](http://www.wago.com/793-5501/000-002)



**Item no.: 793-5501/000-005**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-005](http://www.wago.com/793-5501/000-005)



**Item no.: 793-5501/000-006**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-006](http://www.wago.com/793-5501/000-006)



**Item no.: 793-5501/000-007**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-007](http://www.wago.com/793-5501/000-007)



**Item no.: 793-5501/000-012**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-012](http://www.wago.com/793-5501/000-012)



**Item no.: 793-5501/000-017**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-017](http://www.wago.com/793-5501/000-017)



**Item no.: 793-5501/000-023**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

[www.wago.com/793-5501/000-023](http://www.wago.com/793-5501/000-023)



**Item no.: 793-5501/000-024**  
WMB marking card; as card; stretchable 5 - 5.2 mm; plain; snap-on type

















[www.wago.com/793-5501/000-024](http://www.wago.com/793-5501/000-024)

#### Protective Warning Marker



**Item no.: 2002-115**  
Protective warning marker; with high-voltage symbol, black; for 5 terminal blocks

[www.wago.com/2002-115](http://www.wago.com/2002-115)

|  |  |  |
|--|--|--|
|    | <b>Item no.: 2009-309</b><br>Operating tool; Blades: 3.5 mm and 2.5 mm; for TOPJOB®S installation terminal blocks  | <a href="http://www.wago.com/2009-309">www.wago.com/2009-309</a> |
|    | <b>Item no.: 2009-310</b><br>Operating tool; Blades: 3.5 mm and 5.5 mm; for TOPJOB®S installation terminal blocks  | <a href="http://www.wago.com/2009-310">www.wago.com/2009-310</a> |
|    | <b>Item no.: 210-658</b><br>Operating tool with partially insulated shaft; Blade (3.5 x 0.5) mm; short; angled   | <a href="http://www.wago.com/210-658">www.wago.com/210-658</a>   |
|    | <b>Item no.: 210-720</b><br>Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm  | <a href="http://www.wago.com/210-720">www.wago.com/210-720</a>   |
| <b>ferrule</b>   |  |  |
|     | <b>Item no.: 216-241</b><br>Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90  | <a href="http://www.wago.com/216-241">www.wago.com/216-241</a>   |
|     | <b>Item no.: 216-242</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 | <a href="http://www.wago.com/216-242">www.wago.com/216-242</a>   |
|     | <b>Item no.: 216-243</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90    | <a href="http://www.wago.com/216-243">www.wago.com/216-243</a>   |
|     | <b>Item no.: 216-244</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90  | <a href="http://www.wago.com/216-244">www.wago.com/216-244</a>   |
|   | <b>Item no.: 216-246</b><br>Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90  | <a href="http://www.wago.com/216-246">www.wago.com/216-246</a>   |
|   | <b>Item no.: 216-262</b><br>Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90 | <a href="http://www.wago.com/216-262">www.wago.com/216-262</a>   |
|   | <b>Item no.: 216-263</b><br>Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90    | <a href="http://www.wago.com/216-263">www.wago.com/216-263</a>   |
|   | <b>Item no.: 216-264</b><br>Ferrule; Sleeve for 1.5 mm <sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90  | <a href="http://www.wago.com/216-264">www.wago.com/216-264</a>   |
|   | <b>Item no.: 216-266</b><br>Ferrule; Sleeve for 2.5 mm <sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90  | <a href="http://www.wago.com/216-266">www.wago.com/216-266</a>   |
| <b>Carrier rail</b>  |  |  |
|  | <b>Item no.: 210-112</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm   | <a href="http://www.wago.com/210-112">www.wago.com/210-112</a>   |
|  | <b>Item no.: 210-113</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715  | <a href="http://www.wago.com/210-113">www.wago.com/210-113</a>   |
|  | <b>Item no.: 210-114</b><br>Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715   | <a href="http://www.wago.com/210-114">www.wago.com/210-114</a>   |
|  | <b>Item no.: 210-115</b><br>Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18  | <a href="http://www.wago.com/210-115">www.wago.com/210-115</a>   |



mm



**Item no.: 210-118**

Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715

[www.wago.com/210-118](http://www.wago.com/210-118)



**Item no.: 210-196**

Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715

[www.wago.com/210-196](http://www.wago.com/210-196)



**Item no.: 210-197**

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715

[www.wago.com/210-197](http://www.wago.com/210-197)



**Item no.: 210-198**

Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715

[www.wago.com/210-198](http://www.wago.com/210-198)

**check**



**Item no.: 2009-174**

Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks

[www.wago.com/2009-174](http://www.wago.com/2009-174)



**Item no.: 2009-182**

Testing tap; for max. 2.5 mm<sup>2</sup>; tool-free connection for individual test wires 0.08 - 2.5 mm

[www.wago.com/2009-182](http://www.wago.com/2009-182)



**Item no.: 210-136**

Test plug; 2 mm Ø; with 500 mm cable

[www.wago.com/210-136](http://www.wago.com/210-136)

**Insulation stop**



**Item no.: 2002-171**

Insulation stop; 0.25 - 0.5 mm<sup>2</sup>; 5 pieces/strip

[www.wago.com/2002-171](http://www.wago.com/2002-171)



**Item no.: 2002-172**

Insulation stop; 0.75 - 1 mm<sup>2</sup>; 5 pieces/strip

[www.wago.com/2002-172](http://www.wago.com/2002-172)

**assembling**



**Item no.: 2009-304**

Busbar carrier; not suitable for use as end stop; for DIN 35 rail; 1.5 mm thick

[www.wago.com/2009-304](http://www.wago.com/2009-304)



**Item no.: 2009-305**

Busbar carrier; with end stop function and detachable separator plate; for DIN 35 rail; 7.5 mm thick

[www.wago.com/2009-305](http://www.wago.com/2009-305)

**Downloads**

**Documentation**

**Bid Text**

2003-6651

Aug 13, 2018

DOCX  
15.0 kB

Download

**smartDATA**

**CAD data**



3D Download 2003-6651

URL

Download

---

Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.