

Data sheet | Item number: 855-305/250-501


Plug-in current transformer; Primary rated current: 250 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 1

www.wago.com/855-305/250-501



RoHS
Compliant

BOMcheck.net



Item description

Short description:

The 855 Series Plug-In Current Transformers are inductive, single-conductor current transformers. Due to the measurement principle used, these current transformers are exclusively designed for AC network applications.

Features:

- Screwless CAGE CLAMP® connection technology
- Several mounting options available
- Vibration- and shock-resistant
- High mechanical retention forces
- High current-carrying capacity
- Continuous overload of 120 % the nominal primary current
- Low-voltage current transformer for operating voltages up to max. 1.2 kV
- Can be used in 690 V power networks

- UL recognized components

Data

Technical Data

Input – current transformer

Primary rated current	250 A
Rated continuous thermal current I_{cth}	$1.2 \times I_N$
Rated short-time thermal current I_{th}	$60 \times I_N / 1 \text{ s}$ (max. 100 kA/1 s)
Overcurrent limiting factor	FS5 / FS10 (type dependent, see type plate inscription)
Rated frequency	50 ... 60 Hz

Output – Current transformer

Secondary rated current	5 A
Rated power S_r	5 VA
Highest voltage for equipment U_m	$1.2 \text{ kV}_{rms} \text{ AC}$

Measurement error

Accuracy class	1
----------------	---

Safety and protection:

Test voltage	6 kV AC; 50Hz; 1min
--------------	---------------------

Connection data

Connection technology	CAGE CLAMP®
Solid conductor	0.08 ... 4 mm ² / 28 ... 12 AWG
Fine-stranded conductor	0.08 ... 4 mm ² / 28 ... 12 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 Inch

Geometrical Data

Width	60 mm / 2.362 inch
Height	80.9 mm / 3.185 inch
Depth	52 mm / 2.047 inch

Mechanical data

Type of mounting	Current transformers (closed) Secured to mounting plate
------------------	--

Mounting on carrier rail via carrier rail adapter
Mounting on round cable

Material Data

Insulation class	E
Weight	333 g

Environmental Requirements

Surrounding air (operating) temperature	-5 ... 50 °C
Surrounding air (storage) temperature	-25 ... 70 °C
Max. operating altitude	1000 m

Standards and specifications

Conformity marking	CE
Standards/specifications	EN 61869-1; EN 61869-2; UL: E356480

Commercial data

Country of origin	DE
GTIN	4050821749363
Customs Tariff No.	85043129900

Approvals / Certificates

UL-Approvals

Logo	Approval	Certificate name
	UL UL Multiple Listings Project Handler	E356480

Compatible products

tools

	Item no.: 210-720 Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm	www.wago.com/210-720
--	--	--

General accessories

	Item no.: 2007-8873 Compact terminal block; for current and voltage transformers	www.wago.com/2007-8873
	Item no.: 2007-8874 Compact terminal block; for current and voltage transformers	www.wago.com/2007-8874
	Item no.: 2007-8875	



Compact terminal block; for current transformer circuit

www.wago.com/2007-8875**Item no.: 2007-8876**

Compact terminal block; for 3-phase current transformer circuit

www.wago.com/2007-8876**Item no.: 2007-8877**

Compact terminal block; for current transformer circuit

www.wago.com/2007-8877**Item no.: 857-550**

Current signal conditioner; Current input signal; Current and voltage output signal; Digital output; Configuration via software; Supply voltage: 24 VDC; 6 mm module width

www.wago.com/857-550**Item no.: 857-569**

Power signal conditioner; Current and voltage input signal; Current and voltage output signal; Digital output; Configuration via software; Supply voltage: 24 VDC; 6 mm module width

www.wago.com/857-569

assembling

**Item no.: 855-9900**

Carrier rail adapter

www.wago.com/855-9900**Item no.: 855-9910**

Quick-mount kit

www.wago.com/855-9910

Downloads

Documentation

Additional Information

Disposal; Electrical and electronic equipment, Packaging	Oct 15, 2018	265.8 kB	Download
--	--------------	----------	----------

Engineering-Software

Software for Interface-Products

Interface Configuration Software SMALL	1.5.4.6	EXE	Download
The full setup only includes the WAGO Interface Configuration Software.	Jan 8, 2018	46.0 MB	
Interface Configuration Software FULL	1.5.4.6	EXE	Download
The full setup, in addition to the WAGO Interface Configuration Software, includes the installation for the Microsoft .NET Framework.	Jan 8, 2018	96.5 MB	

smartDATA

CAD data

3D Download 855-305/250-501	URL	Download
-----------------------------	-----	----------



Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.