



Product information

0975 254 131 (RKWTS 5B) - 0975 254 131/5 M

Industrial Connecting Solutions:I/O Modules:I/O Modules Activ - Stand Alone:Profibus:Accessories:Profibus Data Cables:Overmolded Single Ended Cordsets:0975 254 131 (RKWTS 5B)
http://e-catalog.hirschmann.com/link/57078-24228-255441-219791-219793-219798-220052-221291-377255/en/0975_254_131_0500/uistate

Name	0975 254 131 (RKWTS 5B)
Delivery informations	Cord set, single-ended, M12 Profibus signal cable, molded on one side with M12 female connector with threaded joint, right angled version, B coded, 5 poles, 360° shielding connected to knurled nut, colour coding of the conductor acc. to Euro-standard, PUR jacket, halogen-free, screened, violet, 5 meter.
Availability	available
Product description	
Type	0975 254 131/5 M
Order No.	934 728-002
Description	Cord set, single-ended, M12 Profibus signal cable, molded on one side with M12 female connector with threaded joint, right angled version, B coded, 5 poles, 360° shielding connected to knurled nut, colour coding of the conductor acc. to Euro-standard, PUR jacket, halogen-free, screened, violet, 5 meter.
Note	Technical modifications reserved. The application of these products in harsh environments should always be checked before use. Certifications pending.
Color of housing	black
Number of contacts	5
Product characteristics	Oil resistance, Vibration resistance, Drag chains, EMC resistance
Classification	
Belden class	Profibus Data Cables
Belden brand	Lumberg-Automation
Mechanical data	
Type of plug-in contact	Female connector
Design of housing	angled
Thread	M12
Coding of the M12 round plug connector	B
Environmental conditions	
Environmental temperature	-25 °C ... 80 °C
Degree of protection (IP), mounted	IP67, IP68, IP69k (IEC 60529)
Pollution degree	3
Materials	
Housing material / Molded body	TPU
Contact bearer material	PBT
Contact material	CuSn
Contact material - Surface refinement	Cu/Au
Knurled screw / nut material	CuZn, nickel-plated
Sealing material	FKM
Shield sleeve material	CuZn, tined
Approvals	
Approvals	UL
RoHS 2002/95/EG compliant	yes
Electrical data	
Contact resistance	≤ 5 mΩ
Rated current In	4 A at 40 °C
Rated voltage	60 V AC/DC
Test voltage	1.5 kV eff./60 s
Insulation resistance	> 1 GΩ
Cable	
Cable length	5 m
Cable number	254




Industrial Connecting Solutions:I/O Modules:I/O Modules Activ - Stand Alone:Profibus:Accessories:Profibus Data Cables:Overmolded Single Ended Cordsets:0975 254 131 (RKWTS 5B)

http://e-catalog.hirschmann.com/link/57078-24228-255441-219791-219793-219798-220052-221291-377255/en/0975_254_131_0500/uistate

Cable description	Bus cable Profibus
Color of jacket	violet
Material of outer jacket	PUR
Without halogens as in EN 50267-2-3	✓
shielded	✓
welding spark proof	✗
Outer diameter of the cable	7.6 mm
Number of conductors	2
Cable design	2 x 0.38 mm ²
Conductor design	19 x 0.15 mm
Flame resistant according to standard	IEC 60332-2, CSA FT-2

Picture

Drawing



Belden Deutschland GmbH
Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect.
The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.