

WEICONLOCK® AN 306-60

Technical Datasheet

Create Date: 15.02.2016 - Page 1/1



high viscosity high strength hard to disassemble

Assembly of cylindrical parts for worn out bearing rings and bushings

Technical data

i echnicai data	
Application	Assembly of cylindrical parts; ideal for
	repair of worn out bearings
Features	high viscosity, high strength
Colour	silver
For threaded joints up to	R 2"
Viscosity at +25°C Brookfield	150.000 - 900.000 ht mPa·s
Gap filling capacity max.	0,50 mm
Breakaway strength (Thread)	35 - 45 Nm
Prevailing strength (Thread)	10 - 20 Nm
Shear strength (DIN 54452)	25 - 30 N/mm²
Handling strength at room temperature	15 - 30 min.
Final strength at room temperature	3 - 6 h
Temperature resistance	-60 bis +150 °C

Pretreatment of the surface

In general, WEICONLOCK does not require special pretreatment as slightly oily surfaces (e.g. on as received parts) will be tolerated. However, best results will be achieved on cleaned, degreased parts (use WEICON Surface Cleaner). If required, the parts should be slightly roughened.

Processing

WEICONLOCK is ready for use and should be applied evenly direct from the bottle/tube with the dispensing tip (avoid direct contact of dispensing tip with metal). On press fitted parts and larger cylindrical assemblies a thin and uniform layer should be applied on both surfaces. In the case of threaded blind holes fill sufficient quantity in the bore hole. On screws and bolts, apply WEICONLOCK around the thread

Do not pour back into the bottle any WEICONLOCK fluid which had contact with metal; even smallest metal particles will cause the content of the bottle to cure. In series construction, the use of manual or automatic applicators is recommended.

Storage

WEICONLOCK can be stored in the unopened original container for at least 24 months at room temperature. Keep away from heat sources and direct sunlight. The air in the bottle/tube keeps WEICONLOCK liquid.

Note

Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.

Health and Safety

When using WEICON products, the physical, safety technical, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

*Strength values based on M 10 screws, 8.8 grade, thickness of nut 0,8.d

Static shear strength based on cylindrical parts of abt. Ø 13 mm, tolerance (D-d) = 0.05 mm, I/d = 0.88

WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster P.O. Box 84 60 · DE-48045 Münster Germany

Tel. +49 (0) 251 / 93 22-0 Fax +49 (0) 251 / 93 22-244 Fax +49 (0) 251 / 93 22-233 Export www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216 Dubai · U.A.E

Phone +971 4 880 25 05 Fax +971 4 880 25 09 Mobile +971 50 545 99 83 www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20 Kitchener · Ontario · N2E 2C3

Phone +1 519 896 5252 Fax +1 519 896 5254 Cell +1 519 590 5168 www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi Arifağa Sokak No: 29 Kat: 3 34530 Yenibosna – Istanbul Turkey www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1 547176 Budiu Mic (Targu Mures) www.weicon.com · office@weicon.com