


520 Series Panel Connector



Part Numbers

520-210-002	2 circuit housing
520-210-003	3 circuit housing
520-220-001	Retention clip

Contact code (order separately):

516-290-500	Wire hole
516-290-542	Wire wrap (0.61x1.27x14.4mm)
516-290-520	PCB tail
516-290-590	Loose crimp contacts
516-290-591	Crimp contacts on reel (1,800)

Prices on request for:

1. Housings supplied with contacts assembled
2. Housings with cable tails crimped & assembled

FEATURES

- Utilises EDAC gold-plated, hermaphroditic, contacts producing ultra-reliable connection with four gas-tight mating surfaces: A top quality, yet highly cost-effective, interconnect product.
- Board mount or in-line contact tail options.
- Identical insulator for plug and receptacle enabling one part number to be ordered/stocked
- 2 or 3 way options.
- Clip available to neatly secure mated connector to panel when used in-line.

SPECIFICATIONS

- **Materials:**
Housing and locking clip – Glass-filled thermoplastic
Contacts – Phosphor bronze alloy, all-over gold plate to 10u"
- **Electrical**
Contact rating – 8.5 amperes
Contact resistance – 6 milliohms max.
Insulation resistance – 5,000 megohms min.
Voltage proof – 2,500 volts R.M.S. sea level

EDAC (Europe) Ltd., Brick Close, Kiln Farm,
Milton Keynes, MK11 3JB, United Kingdom

Tel: +44 (0) 1908 569333 Fax: +44 (0) 1908 569444

sales@edac.co.uk

EDAC (Europe) 

www.edac.net